



I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels - # WML-511-502

SIZE:	1.000" W x 0.750" H (25.400 mm W x 19.050 mm H)
MATERIAL:	Repositionable Vinyl Cloth
QTY/UOM:	250/Roll
CATALOG #:	WML-511-502
PRODUCT #:	32415

OVERVIEW SPECIFICATIONS

Description for I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels

Blank, printable, repositionable vinyl cloth labels for the I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus printers.

Specification Of I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels

Application(s): Panel Identification, Through Hole - Top, Wire & Cable Marking

Size: 1.000" W x 0.750" H (25.400 mm W x 19.050 mm H)

Printable Area: 1.000" W x 0.750" H (25.400 mm W x 19.050 mm H)

Max Characters Across: LARGE - I.D. PRO: 7, LS2000: 7. SMALL - I.D. PRO: 10, LS2000: 15

Max Lines of Print: I.D. PRO: 4, LS2000: 8

Label Type / Style: Label

Color: White

Finish: Matte

Qty Per Row: 1

Material Type: Vinyl Cloth

Material Description: Repositionable Vinyl Cloth

Brady Material #: [B-502](#)

Safety Catalog: [pg. 126](#)

Recommended Ribbon Series: R5000, R2000

After Process: Yes, this material will work with this application

Printer Compatibility: BradyMarker XC Plus, I.D. PRO Plus, LS2000

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

Special Properties: Repositionable

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll