HEADER STRAIGHT SOLDER PIN0. 8x0.8 MM WITH THREADED FLANGES PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH





HEADER STRAIGHT SOLDER PIN0. 8x0.8 MM WITH THREADED FLANGES PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING

713-1403/107-000 TO 713-1418/107-000

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	713-1411/107-000
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	22
Height (Height / mm)	13.5
Width (Width / mm)	48.6
Depth (Depth / mm)	13.3
No. of connection Points (No. of connection Points)	22
No. of potentials (No. of potentials)	22
COLOR (COLOR)	schwarz
Comment (Comment)	L = ((No. of poles / 2) -1) x Pin Spacing + 13.6 mm
Dimensions (Dimensions)	1.1 +0.1 mm