



| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 722-739 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 9 |
| Height (Height / mm) | 18.25 |
| Width (Width / mm) | 66.5 |
| Depth (Depth / mm) | 11.6 |
| COLOR (COLOR) | lichtgrau |
| Comment (Comment) | $L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5 \text{ mm} + 1,5 \text{ mm}$ |
| Dimensions (Dimensions) | 1.3 +0.1 mm |