






A



B



PC card drilling dimensions(after plating)  
(thickness 1.60±0.20mm)



C

## TIN LEAD PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER  |
|-------|--------|--------|--------|--------|--------|--------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.21  | 10.96  | D09S24A.PA00 |
| 15    | 39.14  | 33.32  | 25.18  | 24.54  | 19.18  | D15S24A.PA00 |
| 25    | 53.03  | 47.04  | 39.12  | 38.25  | 33.12  | D25S24A.PA00 |
| 37    | 69.32  | 63.50  | 55.68  | 54.71  | 49.68  | D37S24A.PA00 |

Protection: 4 --> flash AU  
6 --> 0.76µ AU

D

## LEAD FREE PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER    |
|-------|--------|--------|--------|--------|--------|----------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.21  | 10.96  | D09S24A.PA00LF |
| 15    | 39.14  | 33.32  | 25.18  | 24.54  | 19.18  | D15S24A.PA00LF |
| 25    | 53.03  | 47.04  | 39.12  | 38.25  | 33.12  | D25S24A.PA00LF |
| 37    | 69.32  | 63.50  | 55.68  | 54.71  | 49.68  | D37S24A.PA00LF |

Protection: 4 --> flash AU  
6 --> 0.76µ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
SEE DRAWING C01-8646-0000

European Views

|                                                                                       |         |            |                                       |        |                                   |  |                                                                                                     |  |                                                                                             |            |      |
|---------------------------------------------------------------------------------------|---------|------------|---------------------------------------|--------|-----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------|------------|------|
| www.fciconnect.com                                                                    |         |            | surface<br>ISO 1302                   |        | tolerance std<br>ISO 406 ISO 1101 |  | projection<br> |  | mm<br> |            |      |
|                                                                                       |         |            | TOLERANCES UNLESS OTHERWISE SPECIFIED |        |                                   |  |                                                                                                     |  |                                                                                             |            |      |
| Dr                                                                                    | JOUBERT | 1996/09/10 | ANGULAR                               | LINEAR | 0.X                               |  | ±0.1                                                                                                |  | size<br>A3                                                                                  | Scale<br>2 |      |
| Eng                                                                                   | PESSON  | 1996/09/10 |                                       |        | 0.XX                              |  | ±0.1                                                                                                |  |                                                                                             |            |      |
| Chr                                                                                   | LEGARE  | 1996/09/10 |                                       |        | 0.XXX                             |  | ±0.1                                                                                                |  |                                                                                             |            |      |
| Appr                                                                                  | LEGARE  | 1996/09/10 | Product family                        |        |                                   |  | D-SUB                                                                                               |  | Spec ref -                                                                                  |            |      |
|  |         |            | FEMALE CONNECTOR STD EUROPE           |        |                                   |  | dwg no                                                                                              |  | C01-8646-0490                                                                               |            | Rev. |
|                                                                                       |         |            | straight solder type for PCB 1.6mm    |        |                                   |  |                                                                                                     |  |                                                                                             |            | D    |
| catalog no                                                                            |         |            | -                                     |        |                                   |  | CUSTOMER                                                                                            |  | sheet                                                                                       | of 1       |      |

| rev | ecn no    | dr  | date       |
|-----|-----------|-----|------------|
| A   | -         | JOU | 1996/09/10 |
| C   | L505-001  | MPE | 2005/03/10 |
| D   | L506-0097 | LGO | 2006/07/28 |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |

A

B

C

D