



### Key Features

- One piece molded construction - no lid. Designed for potting box applications.
- Molded from black general purpose ABS plastic.
- Temperature rated -20° to +94° C.
- 1.0 mm (0.04") wall thickness.

| Part Number | Package Quantity | Units        | Length | Width | Depth |
|-------------|------------------|--------------|--------|-------|-------|
| 1596B109    | 1                | Inches<br>mm | 0.45   | 0.45  | 0.35  |
| 1596B109-10 | 10               |              | 11.5   | 11.5  | 9     |
| 1596B110    | 1                | Inches<br>mm | 0.85   | 0.55  | 0.46  |
| 1596B110-10 | 10               |              | 22     | 14    | 12    |
| 1596B101    | 1                | Inches<br>mm | 0.98   | 0.79  | 0.59  |
| 1596B101-10 | 10               |              | 25     | 20    | 15    |
| 1596B112    | 1                | Inches<br>mm | 0.98   | 0.98  | 0.98  |
| 1596B112-10 | 10               |              | 25     | 25    | 25    |
| 1596B102    | 1                | Inches<br>mm | 1.18   | 0.79  | 0.59  |
| 1596B102-10 | 10               |              | 30     | 20    | 15    |
| 1596B111    | 1                | Inches<br>mm | 1.18   | 1.18  | 0.79  |
| 1596B111-10 | 10               |              | 30     | 30    | 20    |
| 1596B103    | 1                | Inches<br>mm | 1.57   | 1.37  | 0.79  |
| 1596B103-10 | 10               |              | 40     | 35    | 20    |
| 1596B107    | 1                | Inches<br>mm | 1.57   | 1.57  | 0.79  |
| 1596B107-10 | 10               |              | 40     | 40    | 20    |
| 1596B113    | 1                | Inches<br>mm | 1.57   | 1.57  | 1.15  |
| 1596B113-10 | 10               |              | 40     | 40    | 29    |
| 1596B104    | 1                | Inches<br>mm | 1.96   | 1.57  | 1.18  |
| 1596B104-10 | 10               |              | 50     | 40    | 30    |
| 1596B108    | 1                | Inches<br>mm | 1.96   | 1.96  | 1.18  |
| 1596B108-10 | 10               |              | 50     | 50    | 30    |
| 1596B105    | 1                | Inches<br>mm | 2.95   | 1.98  | 1.39  |
| 1596B105-5  | 5                |              | 75     | 50    | 35    |
| 1596B114    | 1                | Inches<br>mm | 2.95   | 2.95  | 1.57  |
| 1596B114-5  | 5                |              | 75     | 75    | 40    |
| 1596B115    | 1                | Inches<br>mm | 3.5    | 2.52  | 1.28  |
| 1596B115-5  | 5                |              | 89     | 64    | 32.5  |
| 1596B106    | 1                | Inches<br>mm | 3.93   | 2.36  | 0.99  |
| 1596B106-5  | 5                |              | 100    | 60    | 25    |