

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15-38-8040

Status:

Active

Overview:

SL™ Modular Connectors

Description:

SL™ Single Row, Female, Version G Receptacle, 4 Circuits



Series

image - Reference only

Documents:

- 3D Model

Product Specification PS-70430 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19880

UL

E29179

General

Product Family

FFC/FPC Connectors

Series

70430

Overview

SL™ Modular Connectors

Product Name

SL™

UPC

800753676923

Physical

Circuits (Loaded)

4

Color - Resin

Black

Contact Position

N/A

Durability (mating cycles max)

25

Entry Angle

Vertical

Flammability

94V-0

Material - Metal

Phosphor Bronze

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polyester Alloy

Net Weight

0.691/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.30mm

PCB Retention

None

PCB Thickness - Recommended

1.60mm, 2.40mm

Packaging Type

Tube

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Plating min - Mating

3.810µm

Plating min - Termination

1.905µm

Polarized to PCB

N/A

Stackable

Yes

Temperature Range - Operating

-40°C to +105°C

Termination Interface: Style

IDT or Pierce

Wire/Cable Type

FFC/FPC

Electrical

Current - Maximum per Contact

1A, 2A

Voltage - Maximum

250V

Material Info

Old Part Number

70430-0143

Reference - Drawing Numbers

Product Specification

PS-70430

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

70430Series

Mates With

SL™ Header 70541 , 70543 , 70545 , 70551
, 70553 , 70555 , 74099 , 70634 , 70107 ,
70018

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

DescriptionProduct #

FFC 2 thru 20 Circuit 0638018550
Termination Kit for
use in the Molex
TM-3000 or TM-4000
press installed
into the TM-42
Replacement Crimp
Module

Manual Ribbon	<u>0638170100</u>
Cable Cutter Hand	
Tool	
Tool Kit for Standard	<u>0622007400</u>
Manual Press FFC	
Standard Manual	<u>0622007800</u>
Press for FFC	
TM-42™ Termination	<u>0622018700</u>
Kit	

This document was generated on 10/16/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-38-8040