

PART NAME: PLASTIBOX (STYLE "G")

PART No.: PSP-11573

The drawing includes the following views and dimensions:

- Front View:** Shows the main body with dimensions: 3.437 (width), 2.256 (height), 0.945 (top flange), 0.656 (bottom flange), 0.088 (thickness), and 0.168 (base).
- Side View:** Shows the profile with dimensions: 0.659 (top flange), 2.118 (width), 3.437 (total width), 0.918 (top flange), 2.307 (total width), 0.386 (thickness), 3.906 (width), 3.370 (width), and 0.918 (thickness).
- Section A-A:** Shows the internal structure with dimensions: 7.255 (INSIDE), 0.236, 0.090, 0.227, 0.126, 0.094, 0.331, 1.050 (INSIDE), 0.295, 0.051, 0.094, 0.315, 1.634, 2.265, 2.116 (INSIDE), 0.386, 0.918, 2.307, 3.906 (INSIDE), 3.370, 4.704, 1.794, 0.268, 4.142, 3.605, 0.270, 7.491, 4.199, 1.55°, 4.535, 2.312, 0.398 (R0.265 TYP.), 1.673, 3.346, 6.850, 0.295, 0.709, 0.319, 3.504, 0.717, 0.591, 1.320, and R0.079.
- Base and Cover:** Shows the base and cover with dimensions: 4.142, 3.605, 0.270, 7.491, 4.199, 1.55°, 4.535, 2.312, 0.398 (R0.265 TYP.), 1.673, 3.346, 6.850, 0.295, 0.709, 0.319, 3.504, 0.717, 0.591, 1.320, and R0.079.
- Solid Panel:** Shows the solid panel with dimensions: 3.437, 2.256, 0.088, and 0.168.

MATERIAL - HIGH-IMPACT ABS
COLOR - BLACK
FINISH - TEXTURED BODY WITH SMOOTH TOP INSERT AREA
* - SMOOTH AREA
(4) M3 x 25.4mm SCREWS INCLUDED.
ALL DIMENSIONS HAVE ±0.015 TOLERANCE.