


# Harness Specification Sheet



| Drawing Number | Part Number        | Contact No. (A) | Wire (B)  |        |            | Wire Specification<br>Ins O/D | Terminal Specification | Wire Length<br>(C) | Associated Connector System |
|----------------|--------------------|-----------------|-----------|--------|------------|-------------------------------|------------------------|--------------------|-----------------------------|
|                |                    |                 | Wire Size | Colour | Wire Style |                               |                        |                    |                             |
| JUKMH-578-00   | 01SZESZE-26L150    | SZE-002T-P0.3   | 26 AWG    | BLUE   | UL1061     | 0.98 mm                       | 1.00 - 1.20 mm         | 150mm              | ZE                          |
| JUKMH-579-00   | 01SZESZE-26L300    | SZE-002T-P0.3   | 26 AWG    | BLUE   | UL1061     | 0.98 mm                       | 1.00 - 1.20 mm         | 300mm              | ZE                          |
| JUKMH-580-00   | 01SVTSVT-16L150    | SVT-41T-P1.1    | 16AWG     | BLACK  | UL1015     | 3.40 mm                       | 2.70 - 3.90 mm         | 150mm              | VT                          |
| JUKMH-581-00   | 01SVTSVT-16L300    | SVT-41T-P1.1    | 16AWG     | BLACK  | UL1015     | 3.40 mm                       | 2.70 - 3.90 mm         | 300mm              | VT                          |
| JUKMH-582-00   | 01SZNSZN-26L150    | SZN-002T-P0.7K  | 26 AWG    | BLUE   | UL1061     | 0.98 mm                       | 0.80 - 1.10 mm         | 150mm              | SZN                         |
| JUKMH-583-00   | 01SZNSZN-26L300    | SZN-002T-P0.7K  | 26 AWG    | BLUE   | UL1061     | 0.98 mm                       | 0.80 - 1.10 mm         | 300mm              | SZN                         |
| JUKMH-584-00   | 01SANSAN-26L150    | SAN-002T-0.8A   | 26 AWG    | BLUE   | UL1061     | 0.98 mm                       | 0.90 - 1.30 mm         | 150mm              | SAN                         |
| JUKMH-585-00   | 01SANSAN-26L300    | SAN-002T-0.8A   | 26 AWG    | BLUE   | UL1061     | 0.98 mm                       | 0.90 - 1.30 mm         | 300mm              | SAN                         |
| JUKMH-586-00   | 01SJNSJN-26L150    | SJN-002PT-0.9   | 26 AWG    | BLUE   | UL1007     | 1.28 mm                       | 0.90 - 1.40 mm         | 150mm              | SJN                         |
| JUKMH-587-00   | 01SJNSJN-26L300    | SJN-002PT-0.9   | 26 AWG    | BLUE   | UL1007     | 1.28 mm                       | 0.90 - 1.40 mm         | 300mm              | SJN                         |
| JUKMH-588-00   | 01SCNSCN-22L150    | SCN-001T-1.0    | 22 AWG    | GREY   | UL1007     | 1.56 mm                       | 0.90 - 1.70 mm         | 150mm              | SCN                         |
| JUKMH-589-00   | 01SCNSCN-22L300    | SCN-001T-1.0    | 22 AWG    | GREY   | UL1007     | 1.56 mm                       | 0.90 - 1.70 mm         | 300mm              | SCN                         |
| JUKMH-590-00   | 01SDNSDN-18L150    | SDN-21T-P1.5    | 18 AWG    | BLACK  | UL1015     | 2.80 mm                       | 1.60 - 3.00 mm         | 150mm              | SDN                         |
| JUKMH-591-00   | 01SDNSDN-18L300    | SDN-21T-P1.5    | 18 AWG    | BLACK  | UL1015     | 2.80 mm                       | 1.60 - 3.00 mm         | 300mm              | SDN                         |
| JUKMH-592-00   | 01SPHSPH-26001L150 | SPH-001T-P0.5L  | 26 AWG    | BLUE   | UL1007     | 1.28 mm                       | 1.00 - 1.50 mm         | 150mm              | PH                          |
| JUKMH-593-00   | 01SPHSPH-26001L300 | SPH-001T-P0.5L  | 26 AWG    | BLUE   | UL1007     | 1.28 mm                       | 1.00 - 1.50 mm         | 300mm              | PH                          |
| JUKMH-594-00   | 02XSR02XSR36W50    | 02XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 50mm               | XSR                         |
| JUKMH-595-00   | 02XSR02XSR36W100   | 02XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 100mm              | XSR                         |
| JUKMH-596-00   | 04XSR04XSR36W50    | 04XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 50mm               | XSR                         |
| JUKMH-597-00   | 04XSR04XSR36W100   | 04XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 100mm              | XSR                         |
| JUKMH-598-00   | 06XSR06XSR36W50    | 06XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 50mm               | XSR                         |
| JUKMH-599-00   | 06XSR06XSR36W100   | 06XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 100mm              | XSR                         |
| JUKMH-600-00   | 10XSR10XSR36W50    | 10XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 50mm               | XSR                         |
| JUKMH-601-00   | 10XSR10XSR36W100   | 10XSR-36S       | 36 AWG    | WHITE  | UL11136    | 0.29mm                        | 0.29mm                 | 100mm              | XSR                         |