

Sta-Kon®



Ferrule

T&B Catalog Number:

F4003

UPC Number:

78621033672

Status:

Active

Description:

Insulated Nylon OLD DIN Style Ferrule for Wire Size 16, Wire Size 1.5 mm², Length 0.571 inches, Red

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.

General

Ferrule Type	OLD DIN
Insulation Type	Insulated Nylon
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Wire Range	16
Wire Size (mm ²)	1.50

Dimension Information

A (mm)	14.5
B (mm)	8.0
Diameter C (inches)	.071
Diameter C (mm)	1.8
Diameter D (inches)	.134
Diameter D (mm)	3.4
E (mm)	.15
A (inches)	.571
B (inches)	.315
E (inches)	.006

Specifications


Temperature Rating	105°C
Voltage Rating	300V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	T1, T3, ERG2
Recommended Tool	T1, T3, ERG4

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.02 lbs. per 100



Application Support

T&B Sales Drawings	wsd-000402
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Ferrule dimensions conform to DIN 46228, Part 4.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com