


### ZL262-DG SERIES FEMALE HEADER PITCH 2.54 MM (0.100")




#### Specification:

- 1) To +105° Current Rate: 3 A
- 2) Dielectric Withstanding Voltage: 500 VAC
- 3) Insulation Resistance: 5000 MW
- 4) Temperature: -55°C ~ 105°C
- 5) Insulator: Thermoplastic (UL94V-0)
- 6) Contact: Copper Alloy
- 7) Contact Plated: Gold Flash

| Series No. | No. of Contact (N) |
|------------|--------------------|
| ZL262-10DG | 2 x 5              |
| ZL262-16DG | 2 x 8              |
| ZL262-20DG | 2 x 10             |
| ZL262-26DG | 2 x 13             |
| ZL262-32DG | 2 x 16             |
| ZL262-40DG | 2 x 20             |
| ZL262-50DG | 2 x 25             |
| ZL262-80DG | 2 x 40             |

|            |        |
|------------|--------|
| ZL262-10DG | 2 x 5  |
| ZL262-16DG | 2 x 8  |
| ZL262-20DG | 2 x 10 |
| ZL262-26DG | 2 x 13 |
| ZL262-32DG | 2 x 16 |
| ZL262-40DG | 2 x 20 |
| ZL262-50DG | 2 x 25 |
| ZL262-80DG | 2 x 40 |

Pitch: 2.54 mm



$$A = 2.54 * (N-1)$$

$$B = 2.54 * N$$

All dimensions in mm.