

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	ECR-06-010674	03APR06	RS	FWK

- NOTES:
- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275

2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275

3

Au PLATING

4

Ni PLATING

5

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 4 GHz

NOMINAL IMPEDANCE:50 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:CENTRE CONTACT:1.50 mOhm Max

OUTER CONTACT:0.20 mOhm Max

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A

6

MECHANICAL CHARATERISTICS

COUPLING RETENTION FORCE:N/A

CABLE RETENETION FORCE:N/A




MOUNT NUT RECOMMENDED TORQUE:2.5N

DURABILITY:500 Cycles Min


7

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC



		1	1	PTFE		INSULATION	7
		1	1	BRASS	4	BODY	6
		1	1	BRASS	3	CONTACT	5
		1	1	PTFE		INSULATION	4
		1	1	BRASS	4	SOLDER TAG	3
		1	1	BRASS	4	HEX NUT	2
		1	1	STEEL	4	LOCKWASHER	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		2	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	28NOV05		tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE		
		CHK	28NOV05				
DIMENSIONS:		J.SANDWELL		NAME			
mm		S.PARLOW					
		28NOV05					
		F.WHEELER-KING					
		PRODUCT SPEC					
		—		BNC BULKHEAD SOCKET FRONT MOUNT			
		APPLICATION SPEC		+ TAG 50 OHM			
		—		—			
MATERIAL		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		—		A3	00779	C-1337448	—
		FINISH		CUSTOMER DRAWING			
		—		SCALE		SHEET	REV
				NTS		1 OF 1	D