



Polyethylene
Seal Ring



BUNA-N
O-RING



Seal Rings: Polyethylene, Fiber-Reinforced Plastic

Part Numbers		Thread Type & Size	Dimensions in Inches (mm)		
-22 °F to 158 °F (-30 °C to 70 °C)	- 40 °F to 572 °F (- 40 °C to 300 °C)		A	B	C
			Inner Diameter	Outer Diameter	Height
 Polyethylene	 Fiber-reinforced Plastic	See page 49 for thread specs			
SR-07-NY	SR-07-HD	PG 7	.49 (12.5)	.65 (16.5)	.06 (1.5)
SR-09-NY	SR-09-HD	PG 9	.60 (15.2)	.75 (19)	.06 (1.5)
SR-11-NY	SR-11-HD	PG 11	.73 (18.6)	.89 (22.5)	.06 (1.5)
SR-13-NY	SR-13-HD	PG 13 / 13.5	.80 (20.4)	.98 (25)	.06 (1.5)
SR-16-NY	SR-16-HD	PG 16	.89 (22.5)	1.06 (27)	.06 (1.5)
SR-21-NY	SR-21-HD	PG 21	1.11 (28.3)	1.32 (33.5)	.06 (1.5)
SR-29-NY	SR-29-HD	PG 29	1.46 (37)	1.71 (43.5)	.08 (2)
SR-36-NY	SR-36-HD	PG 36	1.85 (47)	2.17 (55)	.08 (2)
SR-42-NY	SR-42-HD	PG 42	2.13 (54)	2.48 (63)	.08 (2)
SR-48-NY	SR-48-HD	PG 48	2.33 (59.3)	2.72 (69)	.08 (2)
SR-38-NY	-	3/8" NPT	.67 (17)	.87 (22)	.06 (1.5)
SR-18-NY	-	1/2" NPT	.83 (21)	.98 (25)	.06 (1.5)
SR-34-NY	-	3/4" NPT	1.06 (27)	1.43 (36)	.04 (1)
SR-10-02	-	1" NPT	1.32 (33.5)	1.71 (43)	.09 (2.2)
SR-14-NY	-	1-1/4" NPT	.63 (41.5)	1.95 (49)	.06 (1.5)
SM-12-NY	SM-12-HD	M12 x 1.5	.47 (12)	.63 (16)	.08 (2)
SM-16-NY	SM-16-HD	M16 x 1.5	.63 (16)	.79 (20)	.08 (2)
SM-20-NY	SM-20-HD	M20 x 1.5	.79 (20)	.98 (25)	.08 (2)
SM-25-NY	SM-25-HD	M25 x 1.5	.98 (25)	1.22 (31)	.08 (2)
SM-32-NY	SM-32-HD	M32 x 1.5	1.26 (32)	1.50 (38)	.08 (2)
SM-40-NY	SM-40-HD	M40 x 1.5	1.57 (40)	1.96 (48)	.08 (2)
SM-50-NY	SM-50-HD	M50 x 1.5	1.97 (50)	2.28 (58)	.08 (2)
SM-63-NY	SM-63-HD	M63 x 1.5	2.48 (63)	2.83 (72)	.08 (2)

O-Rings: Buna-N, Viton®, Silicone

Part Numbers			Thread Type & Size	Dimensions in Inches (mm)	
-22 °F to 248 °F (-30 °C to 120 °C)	-40 °F to 392 °F (-40 °C to 200 °C)	-76 °F to 482 °F (-60 °C to 250 °C)		D	E
				Inner Diameter	Height
			See page 49 for thread specs		
Buna-N	Viton®	Silicone			
OR-07-BN	OR-07-VT	OR-07-SI		PG 7	.39 (10)
OR-09-BN	OR-09-VT	OR-09-SI	PG 9	.47 (12)	.06 (1.5)
OR-11-BN	OR-11-VT	OR-11-SI	PG 11	.63 (16)	.06 (1.5)
OR-13-BN	OR-13-VT	OR-13-SI	PG 13 / 13.5	.67 (17)	.07 (1.8)
OR-16-BN	OR-16-VT	OR-16-SI	PG 16	.71 (18)	.06 (1.5)
OR-21-BN	OR-21-VT	OR-21-SI	PG 21	1.02 (26)	.08 (2)
OR-29-BN	OR-29-VT	OR-29-SI	PG 29	1.30 (33)	.08 (2)
OR-36-BN	OR-36-VT	OR-36-SI	PG 36	1.69 (43)	.08 (2)
OR-42-BN	OR-42-VT	OR-42-SI	PG 42	1.97 (50)	.08 (2)
OR-48-BN	OR-48-VT	OR-48-SI	PG 48	2.16 (55)	.08 (2)
OR-38-BN	OR-38-VT	OR-38-SI	3/8" NPT	.51 (13)	.08 (2)
OR-18-BN	OR-18-VT	OR-18-SI	1/2" NPT	.75 (19)	.07 (1.8)
OR-34-BN	OR-34-VT	OR-34-SI	3/4" NPT	.91 (23)	.10 (2.5)
OR-10-BN	OR-10-VT	OR-10-SI	1" NPT	1.18 (30)	.10 (2.5)
OR-54-BN	OR-54-VT	OR-54-SI	1-1/4" NPT	1.50 (38)	.10 (2.5)
OR-64-BN	OR-64-VT	OR-64-SI	1-1/2" NPT	1.77 (45)	.10 (2.5)
OM-12-BN*	OM-12-VT	OM-12-SI	M12 x 1.5	.39 (10)	.06 (1.5)
OM-16-BN*	OM-16-VT	OM-16-SI	M16 x 1.5	.47 (12)	.06 (1.5)
OM-20-BN*	OM-20-VT	OM-20-SI	M20 x 1.5	.67 (17)	.07 (1.8)
OM-25-BN	OM-25-VT	OM-25-SI	M25 x 1.5	.87 (22)	.08 (2)
OM-32-BN	OM-32-VT	OM-32-SI	M32 x 1.5	1.14 (29)	.08 (2)
OM-40-BN	OM-40-VT	OM-40-SI	M40 x 1.5	1.38 (35)	.08 (2)
OM-50-BN	OM-50-VT	OM-50-SI	M50 x 1.5	1.69 (43)	.08 (2)
OM-63-BN	OM-63-VT	OM-63-SI	M63 x 1.5	2.17 (55)	.08 (2)

O-Rings & Seal Rings are also available in Viton®. See numbering system above.
To order substitute "BN"(Buna-N) / "NY"(Polyethylene) with "VT".

O-Ring is also available in Silicone. See numbering system above.
To order substitute "BN"(Buna-N) / "NY"(Polyethylene) with "SI".

2) DIMENSIONS [] ARE IN INCHES.

3) DIMENSIONS NOTED ARE FOR REFERENCE ONLY.

Third angle projection



SEALCON

14853 HINDSDALE AVE, SUITE D
CENTENNIAL, CO 80112-4240, USA
TEL: +1-303-699-1135
TOLL FREE: +1-800-456-9012
E MAIL: info@sealconusa.com
WEBSITE: www.sealconusa.com

