

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0507967212](#)
Status: **Obsolete**
Description: Ring Tongue Terminal for 400MCM AWG, Closed Uninsulated Brazed Barrel, Stud Size M14, Oxygen-Free Copper, Length 78.00mm (3.071")

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Ring and Spade Terminals
Series	50796
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	M14
Wire Size AWG	400MCM
Wire Size mm²	250

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-50796-001
---------------	--------------




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[50796Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Japan

Description

Tool Kit For
57343-9012

Product #

[0573439001](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION