






HD15 F (I/O)		SWITCH		HD15 F A&B&C&D	
1	1	1	1	1	1
2	2	2	2	2	2
1:1		1:1		1:1	
14	14	14	14	14	14
15	15	15	15	15	15
SHIELD		SHIELD		SHIELD	

NOTE: All relevant materials are complied with RoHS directive .

6	PLASTO-VISCO-ELASTIC BODY	4	M562
5	SCREW 3*6PWB	4	M805
4	METAL CASE, THICKNESS 0.8mm	1set	M415
3	UL1061 26AWG INSULATOR, LENGTH 150mm	79	M541
	MAIN HEART 5-15-4	1	M94
	SCREW 4*12.5mm WITH PAD	1set	M94
	KNOB FOR A, B, C, D, SWITCH	1	M94
2	HEX-NUT 4.75*13mm, SCREW CAP 4.75*1.5	10set	M95
1	HD15 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	5	M108
No.	DESCRIPTION	Q'TY	Supplier
APPROVED			
CHECKED	RAN		
DRAWING	TIAN	ITEM NO.	SB-474
Cable Length Unless Other Spec Tolerances			
0 ~0.2M ±0.01M			
0.21~1.0M ±0.02M			
1.1 ~1.5M ±0.025M			
1.51~2.1M ±0.03M			
2.1M ↑ ±0.04M			