



DW920K

7.2 Volt Two Position Screwdriver

- Hinged handle with position lock for two grip positions (in-line and pistol grip)
- 15 position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
- Variable speed and reverse switch for added versatility

OVERVIEW

FEATURES

Hinged handle with position lock for two grip positions (in-line and pistol grip)
15 position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
Variable speed and reverse switch for added versatility
Electronic motor brake for better control
Heavy duty quick release chuck
Long life switch with large aluminium heat sink for better heat dissipation and greater durability

STANDARD

1 hour charger
1 battery
Heavy duty carrying case

SPECIFICATIONS

Napájecí napětí	7.2 V
Battery Capacity	NiCd 1.3 Ah
Tool Holder	(Hex) 6.35 mm
Power Output	125 Watts
No Load Speed	0-550 rpm
Max. torque	10 Nm
Hmotnost	1 kg
Length	355 mm
Height	NA mm
Hand/Arm Vibration	<2.5 m/s ²
Uncertainty K 1 (Vibration)	1.5 m/s ²
Sound Pressure	68.35 dB(A)
Uncertainty K 1 (Sound)	
Acoustic Pressure	81.35 dB(A)