

EPC3215G-X





Actual Size

- Used as Trigger Transformer in Photoflash Circuits
- Operating Temperature : -40°C to +85°C
- UL 94V-0 Recognized Components
- UL 1446 Class B Insulation System


Electrical Parameters @ 25° C

PCA Part Number	Voltage (Vdc) V in	Peak Trigger Voltage (V Min.)	Primary OCL @ 0Adc (μ H Typ.) @ 100 KHz, 0.1 Vrms	DCR (Ω Typ.)		Package/ Schematic
				Pri.	Sec.	
EPC3215G-1	300	4000	1.2	0.86	140	A/1
EPC3215G-2	300	4000	1.2	0.86	140	A/2
EPC3215G-3	300	4000	1.7	0.90	169	B/3


Package A





Schematic 1




Schematic 2



Package B



Schematic 3



Unless Otherwise Specified Dimensions are in Inches /mm $\pm .010 / .25$