

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050579515

Status:


Active

Overview:

SL™ Modular Connectors

Description:

SL™ Crimp Housing, Single Row, Version H, Polarized Friction Lock, 15 Circuits



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70058 (PDF)

Product Specification PS-70400 (PDF)

Product Specification PS-71851 (PDF)

Test Summary TS-70058-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	70066
Application	Signal, Wire-to-Board
Comments	Version H
Overview	SL™ Modular Connectors
Product Name	SL™
UPC	800753785229
Physical	
Circuits (maximum)	15
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester Alloy
Net Weight	1.149/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	3.0A
Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Old Part Number

70066-0224

Reference - Drawing Numbers

Product Specification

Sales Drawing

Test Summary

PS-70058, PS-70400, PS-71851

SD-70066-0211-0234

TS-70058-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2014

December 17): No

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

70066 Series

Mates With

6373 Straight Header, 7478 , 171856 ,

171857

Use With

SL™ Crimp Terminal 70058 , 71851

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION