

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301060126](#)
Status: **Active**
Overview: [Stringlights](#)
Description: 5-Lantern Stringlight Cord Set Hand Lamps

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Woodhead
Type	String Lights
UPC	78678834424
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	406.40mm (16.000")
Length	19.81m (65.0')
Material - Guard	N/A
Mounting Style	Stringer
Net Weight	8201.403/g
Packaging Type	Carton
Socket Construction	Rubber Molded
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	40-6157



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130106](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION