

DESIGNERS AND MANUFACTURERS

KEYSTONE

ELECTRONICS CORP.

RoHS COMPLIANT ISO 9001 CERTIFIED

Search By Part number

Check stock by region

HOME

ABOUT US

NEWS

CONTACT US

PRODUCTS

CUSTOM CAPABILITIES

PART BUILDER


GLOBAL DISTRIBUTION

ORDER ONLINE


Polarized PCB Plastic Battery Holders and Retainer Covers

Accommodates CR2 and CR123A Size Lithium Batteries

Thru-Hole Mount



Surface Mount




Thru-Hole Mount

Cat. No. Holders		Cat. No. Covers		Size & Type	Dims.	A	B (Max)	H (ref. Dim)	L	W
1011		1018C		CR2	inch (mm)	1.03 (26.2)	1.36 (34.5)	.658 (16.7)	1.16 (29.4)	.612 (15.5)
1051		1018C		CR123A	inch (mm)	1.36 (34.5)	1.69 (42.9)	.682 (17.3)	1.49 (37.8)	.720 (18.3)
Contacts: .012" (0.3mm) Phosphor Bronze, Tin Nickel Plate										
Surface Mount										
Bulk	On Tape & Reel	Cat. No. Covers		Size & Type	Dims.	A	B (Max)	H (ref. Dim)	L	W
1010	1010TR *	1018C		CR2	inch (mm)	1.03 (26.2)	1.36 (34.5)	.658 (16.7)	1.16 (29.4)	.612 (15.5)
1050	1050TR *	1018C		CR123A	inch (mm)	1.36 (34.5)	1.69 (42.9)	.682 (17.3)	2.05 (52.2)	.720 (18.3)
Contacts: .012" (0.3mm) Phosphor Bronze, Gold Flash over Nickel										

* Supplied on 13" reels - 100 pieces per reel

Base Material: Heat Resistant Nylon, UL rated 94V-0
Temp. Range: -60°F to +293°F (-50°C to +145°C)

Retainer Cover: PBT, UL rated 94V-0
Temp. Range: -60°F to +293°F (-50°C to +145°C)
(see below for detail drawings)



Retainer Cover Material: PBT, UL rated 94V-0
Temp. Range: -60°F to +293°F (-50°C to +145°C)

Cover only Cat. No.	For Holder	H	W
1018C	1050 & 1051	.750 [19.1]	.860 [21.8]

Battery Cross Reference	
Cat. No. 1010, 1010TR & 1011 (CR2)	Cat. No. 1050, 1050TR & 1051 (CR123A Size)
Eveready 544, Duracell PX28L, Kodak K28A & KS28, Panasonic CR14250, Saft LCP3, Electrochem 3B955, Maxell 4LR44, Sanyo CR14250SE	Duracell DL2/3A, Electrochem 3B793 & 3B950, Kodak K123L, Panasonic CR123A, Saft 450SC & VR0450, Sanyo CR17335SE
Battery Reference Dimensions	
CR2 (1/2 AA)	CR123A (2/3A)
.57 [14.5mm] Diameter x .97 [24.6mm] Length	.67 [17.0] Diameter x 1.31 [33.3] Length

[Click to Request Samples](#)

VIEW PRODUCT OVERVIEW