

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC
AF

DIST
50

P

F

ZONE


LTR
C

REVISIONS

DESCRIPTION
REV PER 0041-94

DATE
6/15/94

APPD
JR/SG



- 1 MATES WITH A SPECIAL .020±.001X.110 TAB FOR LANDIS AND GYR.
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .120 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

HOUSING: NYLON, COLOR-RED TRANSLUCENT		2-521010-2	
RECEPTACLE: #3 HARD BRASS			
TIN PL .000080 MIN THK			
MATERIAL & FINISH		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± -	DR 12/4/92 JR RUTH CHK 12/4/92 MS FEHER APPD 12/4/92 D BRATINA APPD 12/4/92 V KARA. PRODUCT SPEC 108-2043	AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL SEE TABLE	FINISH SEE TABLE	NAME RECEPTACLE ASSY, ULTRA-FAST, .110 SERIES, 22-18 AWG	
		SIZE B	FSCM NO 00779
		DRAWING NO 521010	
		SCALE 5:1	SHEET 1 OF 1