

Units: mm

4

3

2


1

500±15mm

100±10

100±10

WHITE  
(W-100#)




P1

①④⑥⑦

①⑤⑥⑦


RED  
(RD-35#)



P2

Mould NO. WM-009 / NM-006

WHITE  
(W-100#)




P3

②④⑦

②⑤⑦



RED  
(RD-35#)



P4

Mould NO. WM-010 / NM-006

PIN ASSIGNMENT:




Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: 2 Ohm(max)
- 3. Insulation resistance: 5Mohm(min)
- 4. dielectric test: DC 300V

NOTE:

1. 小PE袋/大PE袋对应料号, 包袋数量及时间印刷样式:



2. 外箱两个侧袋 ITEM NO 后面各贴一个 35\*22mm ROHS 标签.

|     |            |      |                                                               |
|-----|------------|------|---------------------------------------------------------------|
| ⑩   | TIE        | 2    | BLACK L=80mm                                                  |
| ⑨   | PE BAG     | 1/10 | CLEAR SIZE: 230*300*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS" |
| ⑧   | PE BAG     | 1    | CLEAR SIZE: 100*200*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"   |
| ⑦   | TUBE       | 4    | HEAT SHRINK TUBE BLACK OD1.5*10mm                             |
| ⑥   | IN JACKET  | 3.2g | CLEAR LD-PE(Mould NO. NM-006)                                 |
| ⑤   | OUT JACKET | 6.6g | PVC-40P RED(RD-35)                                            |
| ④   | OUT JACKET | 6.6g | PVC-40P WHITE(W-100)                                          |
| ③   | CABLE      | 1    | NOUL (10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm            |
| ②   | CONN       | 2    | RCA PLUG FEMALE NI-PLATED INSULATOR COLOR:BROWN               |
| ①   | CONN       | 2    | RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN    |
| NO. | NAME       | QTY  | SPECIFICATION                                                 |
| 4   |            |      |                                                               |

|                                           |         |             |                 |
|-------------------------------------------|---------|-------------|-----------------|
| Cnc Tech, LLC                             |         |             |                 |
| Industrial Cable and Connector Technology |         |             |                 |
| DRAWN BY                                  | LICHENG | DRAWING NO. | V6/LJQ-094-081  |
| CHECKED BY                                |         | CUSTOMER    | CNC             |
| APPROVAL BY                               |         | ITEM NO.    | 770-20010-00050 |
| DECIDE BY                                 |         | DATE        | 2012-12-28      |
| VERSIONS / EDITION                        | A/0     | PROJECTION  |                 |


4

W



2

—

Units: mm



## PIN ASSIGNMENT:



*Electrical test:*


1. 100% short, open, miswire test
2. Conduct resistance:  $2\ \Omega$  (max)
3. Insulation resistance:  $5\ \text{Mohm}$  (min)
4. dielectric test: DC 300V

**NOTE:**

1.小PE袋/大PE袋对应料号.包袋数量及时间印刷样式:


**CnC Tech, LLC**  
Industrial Cable and Connector Technology  
770-20010-00100 \_\_\_\_\_  
10PCS, \_\_\_\_\_  
RoHS \_\_\_\_\_  
529 \_\_\_\_\_

2.外箱两个侧壁ITEM NO后面各贴一个35\*22mm ROHS标签。

|                                                                                     |         |                              |
|-------------------------------------------------------------------------------------|---------|------------------------------|
| CNC Tech, LLC                                                                       |         |                              |
| Industrial Cable and Connector Technology                                           |         |                              |
| DRAWN BY                                                                            | LICHENG | DRAWING NO. V6/LJQ-094-081-A |
| CHECKED BY                                                                          |         | CUSTOMER CNC                 |
| APPROVAL BY                                                                         |         | ITEM NO. 770-20010-00100     |
| DECIDE BY                                                                           |         | DATE 2012-12-28              |
| VERSIONS/EDITION                                                                    | A/0     | PROJECTION                   |
|  |         |                              |

# CnC Tech, LLC

# Industrial Cable and Connector Technology

|                  |         |             |                                                                                     |
|------------------|---------|-------------|-------------------------------------------------------------------------------------|
| DRAWN BY         | LICHENG | DRAWING NO. | VG/J0-094-081-A                                                                     |
| CHECKED BY       |         | CUSTOMER    | CNC                                                                                 |
| APPROVAL BY      |         | ITEM NO.    | 770-20010-00100                                                                     |
| DECIDE BY        |         | DATE        | 2012-12-28                                                                          |
| VERSIONS/EDITION | A/0     | PROJECTION  |  |

Units:mm

4

3

2

1

1500±30mm

100±10

100±10

WHITE  
(W-100#)

P1

RED  
(RD-35#)

P2

WHITE  
(W-100#)

P3



RED  
(RD-35#)

P4

Mould NO.WM-009/NM-006

Mould NO.WM-010/NM-006

PIN ASSIGNMENT:



Electrical test:

- 1.100% short,open,miswire test
- 2.Conduct resistance: 2.0hm(max)
- 3.Insulation resistance: 5Mohm(min)
- 4.dielectric test: DC 300V

NOTE:  
1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:



2.外箱两个侧面ITEM NO后面各贴一个35\*22mm ROHS标签.

|     |            |      |                                                               |
|-----|------------|------|---------------------------------------------------------------|
| ⑩   | TIE        | 2    | BLACK L=80mm                                                  |
| ⑨   | PE BAG     | 1/10 | CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS" |
| ⑧   | PE BAG     | 1    | CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"   |
| ⑦   | TUBE       | 4    | HEAT SHRINK TUBE BLACK OD1.5*10mm                             |
| ⑥   | IN JACKET  | 3.2g | CLEAR LD-PE(Mould NO.NM-006)                                  |
| ⑤   | OUT JACKET | 6.6g | PVC-40P RED(RD-35)                                            |
| ④   | OUT JACKET | 6.6g | PVC-40P WHITE(W-100)                                          |
| ③   | CABLE      | 1    | NOUL (10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm            |
| ②   | CONN       | 2    | RCA PLUG FEMALE NI-PLATED INSULATOR COLOR:BROWN               |
| ①   | CONN       | 2    | RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN    |
| NO. | NAME       | QTY  | SPECIFICATION                                                 |

|                                           |         |             |                  |
|-------------------------------------------|---------|-------------|------------------|
| CNC Tech, LLC                             |         |             |                  |
| Industrial Cable and Connector Technology |         |             |                  |
| DRAWN BY                                  | LICHENG | DRAWING NO. | V6/LJ0-094-081-B |
| CHECKED BY                                |         | CUSTOMER    | CNC              |
| APPROVAL BY                               |         | ITEM NO.    | 770-20010-00150  |
| DECIDE BY                                 |         | DATE        | 2012-12-28       |
| VERSION/EDITION                           | A/0     | PROJECTION  |                  |

Units: mm

4

3

2


1

2000±30mm

100±10

100±10

WHITE  
(W-100#)




P1

①④⑥⑦


①⑤⑥⑦

RED  
(RD-35#)



P2

Mould NO. WM-009 / NM-006



WHITE  
(W-100#)

P3

②④⑦

②⑤⑦





RED  
(RD-35#)

P4

Mould NO. WM-010 / NM-006

PIN ASSIGNMENT:



Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: 2 Ohm(max)
- 3. Insulation resistance: 5Mohm(min)
- 4. dielectric test: DC 300V

NOTE:

1. 小PE袋/大PE袋对应料号, 包袋数量及时间印刷样式:

|                 |                                           |
|-----------------|-------------------------------------------|
| CnC Tech, LLC   | Industrial Cable and Connector Technology |
| 770-20010-00200 | 10 PCS                                    |
| 529             | 表示2009年(袋每次产品生产前印刷)                       |

2. 外箱两个侧面ITEM NO后面各贴一个35\*22mm ROHS标签。

|     |            |      |                                                               |
|-----|------------|------|---------------------------------------------------------------|
| ⑩   | TIE        | 2    | BLACK L=80mm                                                  |
| ⑨   | PE BAG     | 1/10 | CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS" |
| ⑧   | PE BAG     | 1    | CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"   |
| ⑦   | TUBE       | 4    | HEAT SHRINK TUBE BLACK OD1.5*10mm                             |
| ⑥   | IN JACKET  | 3.2g | CLEAR LD-PE(Mould NO. NM-006)                                 |
| ⑤   | OUT JACKET | 6.6g | PVC-40P RED(RD-35)                                            |
| ④   | OUT JACKET | 6.6g | PVC-40P WHITE(W-100)                                          |
| ③   | CABLE      | 1    | NOUL (10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm            |
| ②   | CONN       | 2    | RCA PLUG FEMALE NI-PLATED INSULATOR COLOR:BROWN               |
| ①   | CONN       | 2    | RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN    |
| NO. | NAME       | QTY  | SPECIFICATION                                                 |
| 4   |            |      |                                                               |

|                                           |         |             |                  |
|-------------------------------------------|---------|-------------|------------------|
| CnC Tech, LLC                             |         |             |                  |
| Industrial Cable and Connector Technology |         |             |                  |
| DRAWN BY                                  | LICHENG | DRAWING NO. | V6/LJQ-094-081-C |
| CHECKED BY                                |         | CUSTOMER    | CNC              |
| APPROVAL BY                               |         | ITEM NO.    | 770-20010-00200  |
| DECIDE BY                                 |         | DATE        | 2012-12-28       |
| VERSIONS / EDITION                        | A/0     | PROJECTION  |                  |

Units:mm

4

3

2


1

2500±30mm

100±10

100±10

WHITE  
(W-100#)




P1

①④⑥⑦


①⑤⑥⑦

RED  
(RD-35#)



P2

Mould NO.WM-009/NM-006




P3

②④⑦

②⑤⑦



RED  
(RD-35#)



P4

Mould NO.WM-010/NM-006

PIN ASSIGNMENT:



Electrical test:

- 1.100% short,open,miswire test
- 2.Conduct resistance: 2.0hm(max)
- 3.Insulation resistance: 5Mohm(min)
- 4.dielectric test: DC 300V

NOTE:

1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:

|                 |                                           |
|-----------------|-------------------------------------------|
| CnC Tech, LLC   | Industrial Cable and Connector Technology |
| 770-20010-00250 | 10 PCS                                    |
| 529             | 表示2009年(袋每次产品生产前印刷)                       |

2.外箱两个侧面ITEM NO后面各贴一个35\*22mm ROHS标签。


|     |            |      |                                                               |
|-----|------------|------|---------------------------------------------------------------|
| ⑩   | TIE        | 2    | BLACK L=80mm                                                  |
| ⑨   | PE BAG     | 1/10 | CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS" |
| ⑧   | PE BAG     | 1    | CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"   |
| ⑦   | TUBE       | 4    | HEAT SHRINK TUBE BLACK OD1.5*10mm                             |
| ⑥   | IN JACKET  | 3.2g | CLEAR LD-PE(Mould NO.NM-006)                                  |
| ⑤   | OUT JACKET | 6.6g | PVC-40P RED(RD-35)                                            |
| ④   | OUT JACKET | 6.6g | PVC-40P WHITE(W-100)                                          |
| ③   | CABLE      | 1    | NOUL (10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm            |
| ②   | CONN       | 2    | RCA PLUG FEMALE NI-PLATED INSULATOR COLOR:BROWN               |
| ①   | CONN       | 2    | RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN    |
| NO. | NAME       | QTY  | SPECIFICATION                                                 |
| 4   |            |      |                                                               |

CnC Tech, LLC



Industrial Cable and Connector Technology

|                   |         |             |                  |
|-------------------|---------|-------------|------------------|
| DRAWN BY          | LICHENG | DRAWING NO. | V6/LJQ-094-081-D |
| CHECKED BY        |         | CUSTOMER    | CNC              |
| APPROVAL BY       |         | ITEM NO.    | 770-20010-00250  |
| DECIDE BY         |         | DATE        | 2012-12-28       |
| VERSIONS /EDITION | A/0     | PROJECTION  |                  |

Units: mm



PIN ASSIGNMENT:



Electrical test:  
1. 100% short, open, miswire test  
2. Conduct resistance: 2 Ohm(max)  
3. Insulation resistance: 5Mohm(min)  
4. dielectric test: DC 300V

NOTE:  
1. 小PE袋/大PE袋对应料号, 包袋数量及时间印刷样式:

|                     |                                           |
|---------------------|-------------------------------------------|
| CnC Tech, LLC       | Industrial Cable and Connector Technology |
| 770-20010-00500     | 770-20010-00500                           |
| 5 PCS.              | 5 PCS.                                    |
| ROHS                | ROHS                                      |
| 529                 | 529                                       |
| 表示2009年(袋每次产品生产周册印) | 表示2009年(袋每次产品生产周册印)                       |

2. 外箱两个侧面ITEM NO后面各贴一个35\*22mm ROHS标签。

|     |            |      |                                                              |  |
|-----|------------|------|--------------------------------------------------------------|--|
| ⑩   | TIE        | 2    | BLACK L=80mm                                                 |  |
| ⑨   | PE BAG     | 1/10 | CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS" |  |
| ⑧   | PE BAG     | 1    | CLEAR SIZE: 150*280*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"  |  |
| ⑦   | TUBE       | 4    | HEAT SHRINK TUBE BLACK OD1.5*10mm                            |  |
| ⑥   | IN JACKET  | 3.2g | CLEAR LD-PE(Mould NO. NM-006)                                |  |
| ⑤   | OUT JACKET | 6.6g | PVC-40P RED(RD-35)                                           |  |
| ④   | OUT JACKET | 6.6g | PVC-40P WHITE(W-100)                                         |  |
| ③   | CABLE      | 1    | NOUL (10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm           |  |
| ②   | CONN       | 2    | RCA PLUG FEMALE NI-PLATED INSULATOR COLOR:BROWN              |  |
| ①   | CONN       | 2    | RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN   |  |
| NO. | NAME       | QTY  | SPECIFICATION                                                |  |

CnC Tech, LLC

Industrial Cable and Connector Technology

|                  |         |             |                  |
|------------------|---------|-------------|------------------|
| DRAWN BY         | LICHENG | DRAWING NO. | V6/LJ0-094-081-E |
| CHECKED BY       |         | CUSTOMER    | CNC              |
| APPROVAL BY      |         | ITEM NO.    | 770-20010-00500  |
| DECIDE BY        |         | DATE        | 2012-12-28       |
| VERSIONS/EDITION | A/0     | PROJECTION  |                  |