






1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED.
- 3

TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 4

TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 5

MAXIMUM DIMENSION FOR I.C. SEATING PLANE.



	4	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641262-4
OBSOLETE	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641262-3
OBSOLETE	3	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641262-2
	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641262-1
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	09JAN01	AMP Tyco Electronics Corporation Harrisburg, PA 17105		
		OK H WYNKOOP	24AUG00			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD H WYNKOOP	24AUG00	NAME
		0 PLC ± -		PRODUCT SPEC		SOCKET ASSY, DIP, RET LEG, 16 POS, DIPLOMATE™ DL -
		1 PLC ± -		108-1066		
		2 PLC ± -		APPLICATION SPEC		
3 PLC ± .005		4 PLC ± -		114-1049		
ANGLES ± -						
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -		SIZE A1		CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C=641262		RESTRICTED TO -
				SCALE 5:1		SHEET 1 OF 1
						REV S

0.036±.003 TYP

⌀

Ø.009

M