

# MIL-F-23419 military qualified instrument type environmental tested fuses

**Military specification - MIL-F-23419/01 - 0.270"x0.25" pin type fuses**

FM01A125V1/100A  
FM01A125V1/64A  
FM01A125V1/32A  
FM01A125V1/16A  
FM01A125V1/10A  
FM01A125V1/8A  
FM01A125V2/10A  
FM01A125V1/4A  
FM01A125V3/10A  
FM01A125V4/10A  
FM01A125V1/2A  
FM01A125V6/10A  
FM01A125V3/4A  
FM01A125V1A  
FM01A125V11/2A  
FM01A125V2A  
FM01A125V3A  
FM01A125V4A  
FM01A125V5A

\*\*Commercial version is GMW Series.

**Military specification - MIL-F-23419/08 - 0.093" x 0.281" fuses**

FM08A125V1/8A  
FM08A125V1/4A  
FM08A125V3/8A  
FM08A125V1/2A  
FM08A125V3/4A  
FM08A125V1A  
FM08A125V11/2A  
FM08A125V2A  
FM08A125V21/2A  
FM08A125V3A  
FM08A125V4A  
FM08A125V5A  
FM08A125V7A  
FM08A125V10A  
FM08A32V15A

\*\*Commercial version is AH Series. AH Series is obsolete - for reference only.

**Military specification - MIL-F-23419/09 - 1/4" x 1-1/4" fusest**

FM09A250V1/2A  
FM09A250V3/4A\*  
FM09A250V1A\*  
FM09A250V11/4A  
FM09A250V11/2A\*  
FM09A250V2A\*  
FM09A250V3A\*  
FM09A250V4A\*  
FM09A250V5A\*  
FM09A250V6A\*  
FM09A250V8A\*  
FM09A250V10A  
FM09A250V12A  
FM09A250V15A  
FM09A125V20A

\*\*Commercial version is ABC Series. See Data Sheet 2000 for more information.

**Military specification - MIL-F-23419/09 - 1/4" x 1-1/4" fusest**

FM09B250V1/10A  
FM09B250V1/8A  
FM09B250V1/4A  
FM09B250V3/10A  
FM09B250V3/8A  
FM09B250V1/2A  
FM09B250V6/10A  
FM09B250V3/4A  
FM09B250V8/10A  
FM09B250V1A  
FM09B250V11/4A  
FM09B250V11/2A  
FM09B250V16/10A  
FM09B250V2A  
FM09B250V21/2A  
FM09B250V28/10A  
FM09B250V3A  
FM09B250V32/10A  
FM09B125V4A  
FM09B125V5A  
FM09B125V61/4A  
FM09B125V7A  
FM09B125V8A  
FM09B125V10A  
FM09B125V12A  
FM09B125V15A  
FM09B125V20A

\*\*Commercial version is MDA Series. See Data Sheet 2002 for more information.

**Military Specification MIL-F-23419/03** - FM03 series cancelled August 1977. Replaced by FM09A\* series.

**Military Specification MIL-F-23419/06** - FM06 series cancelled. Replaced by FM09B†† series. FM01 Series unavailable with plating options.

FM08 Series can be tin-plated except the 15A. Suffix the letter "T" to the Type Designation Number; i.e. "FM08A125V3/4A."

\* FM09A Series can be silver-plated. Suffix the letter "S" to the Type Designation Number; i.e. "FM09A1-1/2AS."

††FM09B Series unavailable with plating options.

\*\*Commercial equivalent part number is for basic design reference only. Not intended to be used as a substitute for the military part number.

† These government designations are obsolete. Their appearance in this table is for historical reference only.



The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
Eaton.com

Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
Eaton.com/bussmannseries

© 2018 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 2090 — BU-SB09580  
October 2018

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **Eaton.com/bussmannseries**

Follow us on social media to get the latest product and support information.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Eaton:

[FMX-20](#) [FM01A125V3A](#) [FMX-30](#) [FMX-60](#) [FMX-50](#) [FMX-40](#) [FM01A125V5A](#) [FM01A125V1A](#) [FM08A125V1AT](#)  
[FM08A125V5A](#) [FM08A32V15AT](#) [FMG-218](#) [FMX-25LP](#) [FMX-50LP](#) [FMX-60LP](#) [FMX-40LP](#) [FMX-20LP](#) [FMX-30LP](#)  
[FM09A250V8A](#) [FM08A125V10A](#) [FM08A125V1-1/2A](#) [FM08A125V2-1/2A](#) [FM01A125V2A](#) [FM08A125V1A](#)  
[FM08A125V7A](#) [FM09A250V1A](#) [FM09A250V3A](#) [FM08A125V10AT](#) [FM08A125V1/2A](#) [FM08A125V2A](#)  
[FM08A125V3/4A](#) [FM08A125V3A](#) [FM08A125V4A](#) [FM08A125V5AT](#) [FM08A32V15A](#) [FM09A250V1-1/4A](#)  
[FM09A250V12A](#) [FM09A250V15A](#) [FM09A250V2A](#) [FM09A250V6AS](#) [FM09B125V10A](#) [FMM-15](#) [FMM-20](#)  
[FM01A125V1/100A](#) [FM08A125V3/8A](#) [FM08A125V1/2AT](#) [FM01A125V4/10A](#) [FM09B125V5A](#) [FM01A125V4A](#)  
[FM01A125V3/10A](#) [FM08A125V1/4A](#) [FM09B250V1A](#) [FM01A125V1/16A](#) [FM01A125V1/10A](#) [FM08A125V3AT](#)  
[FM09B250V3.2A](#) [FM08A125V7AT](#) [FM09A250V4A](#) [FM09B250V2A](#) [FM09B250V8/10A](#) [FM09A250V1AS](#)  
[FM08A125V4AT](#) [FM09A250V6A](#) [FM09A250V8AS](#) [FM09B250V1-1/2A](#) [FM09B250V3/8A](#) [FM08A125V1/8A](#)  
[FM08A125V1/4AT](#) [FM08A125V1-1/2T](#) [FM09A250V3/4AS](#) [FM09B125V6-1/4A](#) [FM09B125V7A](#) [FM09B125V15A](#)  
[FM09B125V20A](#) [FM01A125V1/8A](#) [FM08A125V2AT](#) [FM09B250V1/2A](#) [FM09B125V8A](#) [FM09A250V3/4A](#)  
[FM09B250V3A](#) [FM09B250V3/4A](#) [FM09A125V20A](#) [FM09B250V1/4A](#) [FM09B250V3/10A](#) [FM09B250V1.6A](#)  
[FM01A125V6/10A](#) [FM09A250V10A](#) [FM09A250V1-1/2A](#) [FM09B125V12A](#) [FM09B250V1/8A](#) [FM09B250V2-1/2A](#)  
[FM09A250V3AS](#) [FM01A125V3/4A](#) [FM09A250V2AS](#) [FM09B125V4A](#) [FM01A125V1/4A](#) [FM09A250V1-1/2S](#)  
[FM01A125V1/2A](#) [FM09A250V5A](#) [FM09B250V1/10A](#)