



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with *PANDUIT*® cable ties for a complete wire routing solution

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

Part Number: ABMM-AT-C0
Product Family: 4-Way Adhesive Backed Cable Tie Mounts
Product Line: Adhesive Backed

Product Line: Adhesive Mounts

RoHS Compliancy Status: Compliant

Part Description: 4-Way Adhesive Backed Cable Tie Mount

Product Type: Cable Tie Mounts - Adhesive Backed

Material: Weather Resistant ABS

Color: Black

UL Recognized: E136577

Height (In.):	.18
Height (mm):	4.6
Length (In.):	.75
Length (mm):	19.1
Width (In.):	.75
Width (mm):	19.1
Adhesive Type:	Acrylic
CE Compliant:	CT-ACC1 / 10.96
Environment:	Outdoors/High Temp
Max. Static Load (g):	136
Max. Static Load (Lbs.):	.30
Mounting Method:	Adhesive Backed
Std. Pkg. UOM:	PK
Used With Cable Ties:	M, I
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100