



Quick Reference

Search by part #

Products

Browse Products

-By Device-



-By Product Line-



-Attachment Methods



-Interface Materials-



-Accessories-



Useful Links

[MSDS Safety Sheets](#)
[How to Order?](#)
[Find Sales Rep](#)
[Find Distributor](#)
[Sample Request](#)
[Quote Request](#)
[Catalog Request](#)
[Building a Part #](#)
[Part # Cross Ref](#)

Products | The Max Clip System™ | Search Results

Max Clip System™
Max Clips



Part Number: **CLP212G**

Clip over edge


RoHS
Compliant



Force: 21 N [4.7 lbs]

Width: 10 mm [0.39 in]

Thickness: 0.5 mm [0.02 in]



Part Number: **CLP212MG**


Clip over edge

RoHS
Compliant

Force: 36 N [8.1 lbs]

Width: 15 mm [0.59 in]

Thickness: 0.6 mm [0.02 in]



Part Number: **CLP212PG**


Clip over edge

RoHS
Compliant

Force: 21 N [4.7 lbs]

Width: 10 mm [0.39 in]

Thickness: 0.5 mm [0.02 in]



Part Number: **CLP212SG**


Clip over edge

RoHS
Compliant

Force: 20 N [4.5 lbs]

Width: 7 mm [0.28 in]

Thickness: 0.5 mm [0.02 in]



Part Number: **CLP212TG**

Clip over edge

RoHS
Compliant

Force: 34 N [7.6 lbs]

Width: 10 mm [0.39 in]

Thickness: 0.6 mm [0.02 in]

