


(5,08 mm) .200"

HPF SERIES



POWER SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?HPF

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Sn over

50μ" (1,27 μm) Ni

Insertion Depth:

(3,68 mm) .145" to (8,26 mm)

.325" (.368" (9,35 mm) plus

board thickness minimum for

bottom entry)

Wiping Distance:

(0,38 mm) .015"

Insertion Force:

(Single contact only)

56 oz (15,57 N) avg.

Withdrawal Force:

(Single contact only)

52 oz (14,46 N) avg.

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,15 mm) .006" max (02-10)

(0,20 mm) .008" max (11-20)

RoHS Compliant:

Yes





Mates with:
HPM, HPW

POWER
EYE
CONTACT



CURRENT RATING (PER CONTACT)		
AMBIENT TEMP	HPM/HPF	
	2 PINS	4 PINS
20°C	25A	22A
40°C	24A	19A
60°C	17A	15.5A
75°C	14.4A	12.7A

Surface Mount
or
Through-hole



Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683