

Honeywell Sensing and Control

Search 

3450CMG 80040505

(Home : Products : Sensors » Thermostats » 3450CMG)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6004)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (988)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1409)
- More...



3450CMG Series Ceramic Manual Reset Thermostats

Actual product appearance may vary.

Sales & Service Distributor Inventory 

Overview Specs Documentation Application Notes

Product Specifications

Functional Properties	Open on rise
Reset Type	Manual
Amperage	0.5 A
Voltage	250 Vac/50 Vdc
Operating Temperature	52 °C to 232 °C [125 °F to 450 °F]
Environmental Exposure Range	10 °C to 260 °C [50 °F to 500 °F]
Open Temperature	198.9 °C [390 °F]
Close Temperature	Manual
Open Tolerance	8.3 °C [15 °F]
Dielectric Strength	MIL-STD- 202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD- 202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD- 202, Method 307; 0.050 Ohm
Housing Material	Ceramic
Contact Material	WE -1 gold alloy cross point
Agency Approvals and Standards	UL, CSA, VDE
Mounting	No bracket
Series Name	3450CMG

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

find out more 

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

Click here to contact us 

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

▶ Meet Dr. Larry



my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT



MICRO SWITCH
Anniversary site