

.050" X .050" MICRO STRIPS FTS SERIES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTS

HI-TEMP

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Current Rating:
1.75A @ 80°C ambient
Operating Temp Range:
-55°C to +125°C
Plating:
Sn or Au over 50µ" (1.27µm) Ni
RoHS Compliant:
Yes


Processing:

Max Processing Temp:
230°C for 60 seconds, or
260°C for 20 seconds 3x
with Matte Sn plating
Lead-Free Solderable:
Wave, or reflow with
Matte Sn plating
SMT Lead Coplanarity:
.004" (0.10mm) max

Note: Some lengths, styles and options are non-standard, non-returnable.

Mates with:
FFSD, CLP, FLE, SFMC(LIF)

OPTIONS



Mates with
socket strips
or IDC cable

Surface mount
or through hole

Low profile
(1.27mm) .050"

Micro pitch
.050" x .050"
(1.27mm x 1.27mm)

Shrouded and
alignment pin
options available
(patent pending)

ALSO AVAILABLE

Single row (Mates to CLP Series).
Call Samtec.

FTS

1

NO. PINS
PER ROW

LEAD
STYLE


PLATING
OPTION

ROW
OPTION


OTHER
OPTION

02 thru 50

(except -S & -SA option = 05 thru 46)



LEAD STYLE	A
-01	(3,05) .120
-02	(1,91) .075
-03	(1,65) .065



-01
= .120 (3,05)
Post (Mates
with FFSD)

-02
= .075 (1,91)
Post (Mates
with FLE)

-03
= .065 (1,65)
Post (Mates
with CLP)

-L
= 10µ" (0,25µm)
Gold on post,
Matte Tin
on tail

-F
= Gold flash
on post,
Matte Tin
on tail

-DV
= Double
Vertical SMT


-D
= Double
Row Through
Hole

-SA
= Shrouded with
Alignment Pin
(05 thru 46
positions. Style
-02 & -03 only.
-SV not available.)


-S
= Shrouded
(05 thru 46
positions. Style
-02 & -03 only.
-SV not available.)

-P
= Pick & Place
(05 positions
minimum)
Pad (-SV & -S
not available)


-TR
= Tape & Reel
(-SV & -DV only)




(Shrouded options removed for clarity)



-SA OPTION



-S OPTION



-P OPTION

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
SAMTEC NORDIC/BALTIC • Tel: +46-84477280 • Fax: +46-87420413
SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-5423 4575
SAMTEC SOUTH AFRICA • Tel: 27 11 454 4317 • Fax: 27 86 6714432
SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
SAMTEC INDIA • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187
SAMTEC TAIWAN • Tel: 886-2-2735-6109 • Fax: 886-2-2735-5036
SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745