


Instrument Case (1454 Series)



KEY FEATURES

Part Number	Units	Dimensions		
		A	B	C
1454C	inch	4	2.5	2
	mm	102	64	51
1454J	inch	4	3	4
	mm	102	76	102
1454M	inch	4	3	6
	mm	102	76	152
1454E	inch	4	5	2
	mm	102	127	51
1454F	inch	4	6	3
	mm	102	152	76
1454R	inch	5	5	7.5
	mm	127	127	191
1454L	inch	5	6	4
	mm	127	152	102
1454H	inch	5	7.5	2.5
	mm	127	191	64
1454D	inch	5.875	4	2.125
	mm	149	102	54
1454DD	inch	5.875	5.187	2.75
	mm	149	132	70
1454G	inch	6	2.5	2
	mm	152	64	51
1454K	inch	8	3.5	2.5
	mm	203	89	64
1454N	inch	8	6	3
	mm	203	203	76
1454P	inch	10	5	3.5
	mm	254	127	89
1454S	inch	10	6	3
	mm	254	203	76
1454W	inch	12	8	3
	mm	305	203	76

- Made of strong, economical 20 gauge steel.
- Contempra grey panels with textured black covers (powder paint).
- Choice of sloping or vertical front panels by reversing case.
- 6-32 Philips nickel plated screws and self-adhesive rubber feet included.
- Replacement screws **1421J6** (Pkg. of 6, 6-32 Philips head screws).



Notes: - Models with "B" dimension less than 5" (127 mm) have only one hole per side, centered in "B".

Metal



CANADA
Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010
USA
Cheektowaga, NY (716) 651-0086

www.hammondmfg.com

EUROPE
Basingstoke, UK +44 1256 812812

AUSTRALASIA
Queenstown, SA, Australia +61 8 8240 2244