

FJ-05-D-04.80-2

FJ SERIES


FLAT FLEXIBLE CABLE (FFC) JUMPER

Mates with:
FC1, ZF1

Conductor:
Tin Plated Copper
Conductor Resistance:
300 Ω /km max
Insulation Resistance:
12 M Ω /km min
(conductor-to-conductor)
Dielectric Test:
400 VAC during 1 minute
(conductor-to-conductor)
Temperature Rating:
-30°C to +80°C
Voltage Rating:
300 VAC
Flame Resistance:
VW-1 (UL 758)
RoHS Compliant:
Yes



Variable
lengths



Note: Some sizes, styles and options are non-standard, non-returnable.