


C-CD-503-02

- WIRE SIZE: 12 - 10 AWG
4.0 - 6.0 MM²



INCHES	MM
0	0
1	25.4
2	50.8
3	76.2
4	101.6
5	127.0
6	152.4
7	177.8
8	203.2
9	228.6
10	254.0
11	279.4
12	304.8
13	330.2
14	355.6
15	381.0
16	406.4
17	431.8
18	457.2
19	482.6
20	508.0
21	533.4
22	558.8
23	584.2
24	609.6
25	635.0
26	660.4
27	685.8
28	711.2
29	736.6
30	762.0
31	787.4
32	812.8
33	838.2
34	863.6
35	889.0
36	914.4
37	939.8
38	965.2
39	990.6
40	1016.0
41	1041.4
42	1066.8
43	1092.2
44	1117.6
45	1143.0
46	1168.4
47	1193.8
48	1219.2
49	1244.6
50	1270.0
51	1295.4
52	1320.8
53	1346.2
54	1371.6
55	1397.0
56	1422.4
57	1447.8
58	1473.2
59	1498.6
60	1524.0
61	1549.4
62	1574.8
63	1600.2
64	1625.6
65	1651.0
66	1676.4
67	1701.8
68	1727.2
69	1752.6
70	1778.0
71	1803.4
72	1828.8
73	1854.2
74	1879.6
75	1905.0
76	1930.4
77	1955.8
78	1981.2
79	2006.6
80	2032.0
81	2057.4
82	2082.8
83	2108.2
84	2133.6
85	2159.0
86	2184.4
87	2209.8
88	2235.2
89	2260.6
90	2286.0
91	2311.4
92	2336.8
93	2362.2
94	2387.6
95	2413.0
96	2438.4
97	2463.8
98	2489.2
99	2514.6
100	2540.0

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.				AVAILABLE STUD SIZES	
C-541-	.375 <u>9.53</u>	.301 <u>7.65</u>	1.232 <u>31.29</u>				06,08,10	
C-568-	.533 <u>13.54</u>	.393 <u>9.98</u>	1.385 <u>35.18</u>				10,14,56	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED	REFERENCE REV A DEC 1/83 REV B 1/6/94	SCALE: NTS	DATE	TITLE:				
FRACTION	DEC.	ANG.	CHKD. BY: GZ	11-15-84	SPADE TONGUE TERMINAL AVIKRIMP 500-SERIES			
±	±	±	APPRD. BY:	11-26-84				
					ETC ^{mo} lex INCORPORATED			
					DWG. NO.	A	CUSTOMER DWG	

ETC moex
INCORPORATED

DWG. NO.	A	CUSTOMER DWG
-------------	----------	-----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19196-0068