

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0210390453

Status:

Active - Custom

Overview:

Description:

1.00mm (.039") Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 28 Circuits, 0.152m (6.00") Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                   |
|-------------------------------|-----------------------------------|
| General                       |                                   |
| Product Family                | Cable                             |
| Series                        | 21039                             |
| Comments                      | Contacts on the same side, Type A |
| Geographic Area               | Americas                          |
| Overview                      | Premo-Flex&#153;                  |
| Product Name                  | Premo-Flex™FFC Jumper             |
| Physical                      |                                   |
| Cable Length                  | 0.152m (6.00")                    |
| Circuits (Loaded)             | 28                                |
| Packaging Type                | Bag                               |
| Pitch - Term. Interface (in)  | 0.039 In                          |
| Pitch - Term. Interface (mm)  | 1.00 mm                           |
| Temperature Range - Operating | -40°C to +80°C                    |
| Wire Size AWG                 | N/A                               |
| Wire/Cable Type               | Flat Flex Cable                   |
| Electrical                    |                                   |
| Current - Maximum             | 1.3A                              |
| Voltage - Maximum             | 30V                               |

Material Info



Series image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

Duration at Max. 30  
Process Temperature (seconds)  
Max. Cycles at Max. 1  
Process Temperature  
Process Temperature 250 max. C

Search Parts in this Series  
21039 Series

Use With  
Any 1.00mm (.039") Pitch Molex FFC/FPC connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION