


PART NUMBER	CURRENT RATING (A)	BODY COLOR	RATED VOLTAGE
0283020.MXJ-B	20	LT. BLUE	32V
0283030.MXJ-B	30	PINK	
0283040.MXJ-B	40	GREEN	
0283050.MXJ-B	50	RED	
0283060.MXJ-B	60	YELLOW	
0283070.MXJ-B	70	BROWN	
0283080.MXJ-B	80	BLACK	
0283100.MXJ-B	100	BLUE	
0283120.MXJ-B	120	WHITE	
0283140.MXJ-B	140	REDDISH BROWN	

% OF RATED CURRENT	OPENING TIME	
	MIN	MAX
110%	14,400 SEC.	-
200%	5 SEC.	100 SEC.
350%	0.2 SEC.	7 SEC.
600%	0.04 SEC.	1 SEC.



METRIC

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
MATERIAL SPEC					
COPIES TO					
1	9	18	FINISH	2	1
2	10	19	SCALE	2	1
3	12	20	DATE	08/14/09	2
4	13	21	DRW	GMB	2
5	14	23	CHK	SUPER DR	2
6	15	33	DATE		2
7	16	43	APPD	FINISH GOOD WT	2
8	17	53		GRAMS/PIECE	2
TOLERANCE UNLESS OTHERWISE SPECIFIED					
ONE PLACE DEC +/- .4					
TWO PLACE DEC +/- .25					
THREE PLACE DEC +/- .100					
ANGULAR +/- 1°					
3RD ANGLE PROJECTION					
TITLE FUSE - PAL 283 ATIS 31mm 32V					
SLOW BLOW					
REVISION					
DRAWING NO.					
OUTLINE					
A					
OL-0283000.MXJ-B					