



PART NO	PKG TYPE	QTY
8-36919-3	BOX	25
8-36919-5	BAG	5
36919	BOX	50

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			K2	REVISED PER ECR 09-015243	29JUL09	JR
						APVD
						TM

AMP WIRE RANGE	 Listed FILE E13288
1/0 AWG STRANDED	1/0 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
1/0 AWG STRANDED	MS 20659-135 CLASS 2



- 1


STAMP AMP 1/OW* APPROX AS SHOWN
- 2

MATERIAL THK IS 1.78±0.08 [.070±.003]
- 3

COPPER PER ASTM B-152, ANNEALED
- 4

TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 7/21/91	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: MM [INCHES]		CHK RD HEIM 8/15/91				
		APVD AJ KAUFMAN 8/15/91	NAME TERMINAL, RING TONGUE, SOLISTRAND			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL - 3		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-36919	RESTRICTED TO -
FINISH - 4		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 2	REV K2	

THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.					
PART NO	PKG TYPE	QTY			
36919-1	BOX	50			

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN APVD
		-		SEE SHEET 1	-	- -

AMP
WIRE RANGE

1/0 AWG
SOLID OR STRANDED



- 1 STAMP AMP 1/OW* APPROX AS SHOWN
- 2 MATERIAL THK IS 1.78 $\pm$ 0.08 [.070 $\pm$.003]
- 3 COPPER PER ASTM B-152, ANNEALED
- 4 NICKEL PLATE 0.00762 [.000300] MIN THK PER QQ-N-290

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 7/21/91 DK SCHRUM	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: MM [INCHES]		CHK 8/15/91 RD HEIM				
		APVD 8/15/91 AJ KAUFMAN	NAME			
		PRODUCT SPEC	TERMINAL, RING TONGUE, HEAT RESISITANT STRATO-THERM			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		-	A2	00779	C=36919	-
MATERIAL - 3		FINISH - 4	WEIGHT -	CUSTOMER DRAWING		SCALE 2:1 SHEET 2 of 2 REV K2