

Anna-40-3 series



Ordering number C11711
Description C11711_Anna-40-3-M-XP-G

Family	Anna-40-3	FWHM	28 degrees
Type	Lens	Efficiency	-
LED	XP-G	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Glue, pin		
Status	Ready		



Ordering number C11712
Description C11712_Anna-40-3-W-XP-G








Family	Anna-40-3	FWHM	42 degrees
Type	Lens	Efficiency	-
LED	XP-G	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

D

C

B

A

Anna-3Anna-4Anna-5Anna-6Anna-7

Material: PMMA

Versions:

Anna-3-S

Anna-3-M

Anna-3-W

Anna-4-S

Anna-4-M

Anna-4-W

Anna-5-S

Anna-5-M

Anna-5-W

Anna-6-S


Anna-6-M

Anna-6-W

Anna-7-S

Anna-7-M

Anna-7-W



This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.

LEDILL
T
F
Fe
e
i
iN
nd
h

DRAWING TITLE

Datasheet Anna40-series Lens

DRAWN BY

p

DATE

12.10.2010

CHECKED BY

s

n

DATE

12.10.2010

DESIGNED BY

hh

DATE

30.07.2010

SIZE

A4

DRAWING NUMBER

-

REV

1

SCALE

1:1

WEIGHT (g)

SHEET

1/1

D

A