




OUTSIDE DIAMETER		THREADS PER INCH	DEPTH OF THREAD	RADIUS OF THREAD
MAJOR CREST OF THREAD	MINOR ROOT OF THREAD			
MIN. .206" (5.23mm)	-----	25.4	.011" MIN. (.28mm)	.0116" (.29mm)
MAX. .210" (5.33mm)	MAX. .188" (4.77mm)			

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
1769	2.5	.200	.200	2.51	500	C-2R
373	14.0	.080	.500	6.29	2,500	C-2F
8384	28.0	.040	.200	2.51	50,000	C-2F
335	28.0	.040	.340	4.27	4,000	C-2F
8369	28.0	.065	.650	8.17	5,000	C-2F

METRIC THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE T-1 3/4 STANDARD MIDGET SCREW BASE LAMP			
DRAWN BY L. WENGSTROM		APPV'D BY DATE E.D. 4/9/01		SIZE A	FSCM NO. 55335	DRAWING NO. SCREW BASE T-1 3/4--17.4	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED				SCALE NONE	RELEASED DATE 11/17/00	REVISION DATE 4/9/01	
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	REV. NO. A SHEET 1 OF 1				

REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE
A	DELETE NOTE RELEASE & CANCEL 335LSV	4/9/01 11/17/00