




ISO 5746, DIN ISO 5746, NF E 73-103

- High-frequency hardened cutting edges for power and durability.
- Nose profile combines strength and manoeuvrability.
- 4 options :
 - CPE : Chrome finish, ergonomic grips, return spring.
 - TE : Varnish finish, ergonomic grips, return spring.
 - G : Varnish finish, PVC grips.
 - VE : Varnish finish, return spring, 1000V insulated grips for electrical safety to EN 60900 and , for working on or near live components.



	$\varnothing$ max mm	D	L	A	B	C	
Fe wire 200 kg/mm ²	mm	mm	mm	mm	mm	mm	g
187.16CPE	1,6	12	165	34	21	9,5	195
187.18CPE	1,8	13	185	36	23	10	225
187.20CPE	2	15	205	42	26	11,5	300
187.18TE	1,8	13	185	36	23	10	225
187.20TE	2	15	205	42	26	11,5	300
187.16G	1,6	12	160	34	21	9,5	170
187.18G	1,8	13	180	36	23	10	200
187.20G	2	15	200	42	26	11,5	275
187.16VE	1,6	12	165	34	21	9,5	205
187.18VE	1,8	13	185	36	23	10	235