

Technical Characteristics

Ampere Rating	32A
Application	Constant and Variable Torque
UL Listing	File Number E184727
CSA Listing	File Number 224330
CE Marked	Yes
RoHS Compliant	Yes
Other Certifications	GOST, C-Tick, and CCC
Communication	Modbus
Analog Input	1 PTC Probe
Logic Input	3
Logic/Relay Output	(2) 1 NO/1 NC
Degree of Protection	IP20
Operating Temperature Range	104°F to 140°F (40°C to 60°C) with derating current 2.2% for each degree above 104°F(40°C)
Frame Size	A
Horsepower Rating	7.5HP@208V - 10HP@230V - 11HP@400V - 20HP@460V - 25HP@575V
Motor Power Rating	11kW
Control Voltage	110 Vac
Marketing Trade Name	Altistart
Type	ATS22
Weight	12.1 lbs

Shipping and Ordering

Category	22576 -
Discount Schedule	CP1G
GTIN	00785901687399
Package Quantity	1
Weight	12.59 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	CN

document.