

## TK 77 – Polystyrene and Polycarbonate – 65x65mm (2.56x2.56in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

#### Polystyrene

#### Polycarbonate<sup>1</sup>

| Ordering Information   | Height mm (in)  | Cat. No. | Type       | Cover Color | Std. Pk. | Cat. No. | Type       | Cover Color | Std. Pk. |
|------------------------|-----------------|----------|------------|-------------|----------|----------|------------|-------------|----------|
| Enclosure - low cover  | 57 mm (2.24 in) | 110-401  | PS 77-6-o  | gray        | 5        | 120-401  | PC 77-6-o  | gray        | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 110-901  | PS 77-8-o  | gray        | 5        | 120-901  | PC 77-8-o  | gray        | 5        |
| Enclosure - low cover  | 57 mm (2.24 in) | 111-001  | PS 77-6-to | trans.      | 5        | 130-001  | PC 77-6-to | trans.      | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 111-501  | PS 77-8-to | trans.      | 5        | 130-501  | PC 77-8-to | trans.      | 5        |

### Sidewalls with Metric Knockouts

#### Polystyrene

#### Polycarbonate<sup>1</sup>


| Ordering Information   | Height mm (in)  | Cat. No. | Type       | Cover Color | Std. Pk. | Cat. No. | Type       | Cover Color | Std. Pk. |
|------------------------|-----------------|----------|------------|-------------|----------|----------|------------|-------------|----------|
| Enclosure - low cover  | 57 mm (2.24 in) | 105-401  | PS 77-6-m  | gray        | 5        | 127-401  | PC 77-6-m  | gray        | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 105-901  | PS 77-8-m  | gray        | 5        | 127-901  | PC 77-8-m  | gray        | 5        |
| Enclosure - low cover  | 57 mm (2.24 in) | 106-001  | PS 77-6-tm | trans.      | 5        | 137-001  | PC 77-6-tm | trans.      | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 106-501  | PS 77-8-tm | trans.      | 5        | 137-501  | PC 77-8-tm | trans.      | 5        |

### Accessories

| Ordering Information | Cat. No. | Type       | Std. Pk. |
|----------------------|----------|------------|----------|
| Mounting Plate       | 195-001  | MP77       | 1        |
| DIN Rail TS15-49.5mm | 197-049  | TS 15/49.5 | 1        |
| Hinge Kit Set        | 190-002  | HK1        | 1        |
| Mounting Tab Kit     | 194-001  | MT1        | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions



### Knockout Positions


(all 4 sides)



## TK 97 – Polystyrene and Polycarbonate – 94x65mm (3.70x2.56in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

#### Polystyrene

#### Polycarbonate<sup>1</sup>

| Ordering Information   | Height mm (in)  | Cat. No. | Type       | Cover Color | Std. Pk. | Cat. No. | Type       | Cover Color | Std. Pk. |
|------------------------|-----------------|----------|------------|-------------|----------|----------|------------|-------------|----------|
| Enclosure - low cover  | 57 mm (2.24 in) | 110-402  | PS 97-6-o  | gray        | 5        | 120-402  | PC 97-6-o  | gray        | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 110-902  | PS 97-8-o  | gray        | 5        | 120-902  | PC 97-8-o  | gray        | 5        |
| Enclosure - low cover  | 57 mm (2.24 in) | 111-002  | PS 97-6-to | trans.      | 5        | 130-002  | PC 97-6-to | trans.      | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 111-502  | PS 97-8-to | trans.      | 5        | 130-502  | PC 97-8-to | trans.      | 5        |

### Sidewalls with Metric Knockouts

#### Polystyrene

#### Polycarbonate<sup>1</sup>


| Ordering Information   | Height mm (in)  | Cat. No. | Type       | Cover Color | Std. Pk. | Cat. No. | Type       | Cover Color | Std. Pk. |
|------------------------|-----------------|----------|------------|-------------|----------|----------|------------|-------------|----------|
| Enclosure - low cover  | 57 mm (2.24 in) | 105-402  | PS 97-6-m  | gray        | 5        | 127-402  | PC 97-6-m  | gray        | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 105-902  | PS 97-8-m  | gray        | 5        | 127-902  | PC 97-8-m  | gray        | 5        |
| Enclosure - low cover  | 57 mm (2.24 in) | 106-002  | PS 97-6-tm | trans.      | 5        | 137-002  | PC 97-6-tm | trans.      | 5        |
| Enclosure - high cover | 81 mm (3.19 in) | 106-502  | PS 97-8-tm | trans.      | 5        | 137-502  | PC 97-8-tm | trans.      | 5        |

### Accessories

| Ordering Information | Cat. No. | Type     | Std. Pk. |
|----------------------|----------|----------|----------|
| Mounting Plate       | 195-002  | MP97     | 1        |
| DIN Rail TS15-80mm   | 197-080  | TS 15/80 | 1        |
| Hinge Kit Set        | 190-002  | HK1      | 1        |
| Mounting Tab Kit     | 194-001  | MT1      | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



## TK 99 – Polystyrene and Polycarbonate – 94x94mm (3.70x3.70in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

| Ordering Information |                        | Height mm (in)  | Polystyrene |            |             |          | Polycarbonate <sup>1</sup> |            |             |          |
|----------------------|------------------------|-----------------|-------------|------------|-------------|----------|----------------------------|------------|-------------|----------|
|                      |                        |                 | Cat. No.    | Type       | Cover Color | Std. Pk. | Cat. No.                   | Type       | Cover Color | Std. Pk. |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 110-403     | PS 99-6-o  | gray        | 4        | 120-403                    | PC 99-6-o  | gray        | 4        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 110-903     | PS 99-8-o  | gray        | 3        | 120-903                    | PC 99-8-o  | gray        | 3        |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 111-003     | PS 99-6-to | trans.      | 4        | 130-003                    | PC 99-6-to | trans.      | 4        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 111-503     | PS 99-8-to | trans.      | 3        | 130-503                    | PC 99-8-to | trans.      | 3        |

### Sidewalls with Metric Knockouts

| Ordering Information |                        | Height mm (in)  | Polystyrene |            |             |          | Polycarbonate <sup>1</sup> |            |             |          |
|----------------------|------------------------|-----------------|-------------|------------|-------------|----------|----------------------------|------------|-------------|----------|
|                      |                        |                 | Cat. No.    | Type       | Cover Color | Std. Pk. | Cat. No.                   | Type       | Cover Color | Std. Pk. |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 105-403     | PS 99-6-m  | gray        | 4        | 127-403                    | PC 99-6-m  | gray        | 4        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 105-903     | PS 99-8-m  | gray        | 3        | 127-903                    | PC 99-8-m  | gray        | 3        |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 106-003     | PS 99-6-tm | trans.      | 4        | 137-003                    | PC 99-6-tm | trans.      | 4        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 106-503     | PS 99-8-tm | trans.      | 3        | 137-503                    | PC 99-8-tm | trans.      | 3        |

### Accessories

| Ordering Information  | Cat. No. | Type     | Std. Pk. |
|-----------------------|----------|----------|----------|
| Mounting Plate        | 195-003  | MP99     | 1        |
| DIN Rail TS15 - 80 mm | 197-080  | TS 15/80 | 1        |
| Hinge Kit Set         | 190-002  | HK1      | 1        |
| Mounting Tab Kit      | 194-001  | MT1      | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.



# TK 1111 – Polystyrene and Polycarbonate – 110x110mm (4.33x4.33in.)

## Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



## Smooth Sidewalls

| Ordering Information     |                        | Height mm (in)  | Polystyrene |              |             |          | Polycarbonate <sup>1</sup> |              |             |          |
|--------------------------|------------------------|-----------------|-------------|--------------|-------------|----------|----------------------------|--------------|-------------|----------|
|                          |                        |                 | Cat. No.    | Type         | Cover Color | Std. Pk. | Cat. No.                   | Type         | Cover Color | Std. Pk. |
| <input type="checkbox"/> | Enclosure - low cover  | 66 mm (2.60 in) | 110-404     | PS 1111-7-o  | gray        | 3        | 120-404                    | PC 1111-7-o  | gray        | 3        |
| <input type="checkbox"/> | Enclosure - high cover | 90 mm (3.54 in) | 110-904     | PS 1111-9-o  | gray        | 3        | 120-904                    | PC 1111-9-o  | gray        | 3        |
| <input type="checkbox"/> | Enclosure - low cover  | 66 mm (2.60 in) | 111-004     | PS 1111-7-to | trans.      | 3        | 130-004                    | PC 1111-7-to | trans.      | 3        |
| <input type="checkbox"/> | Enclosure - high cover | 90 mm (3.54 in) | 111-504     | PS 1111-9-to | trans.      | 3        | 130-504                    | PC 1111-9-to | trans.      | 3        |

## Sidewalls with Metric Knockouts


| Ordering Information     |                        | Height mm (in)  | Polystyrene |              |             |          | Polycarbonate <sup>1</sup> |              |             |          |
|--------------------------|------------------------|-----------------|-------------|--------------|-------------|----------|----------------------------|--------------|-------------|----------|
|                          |                        |                 | Cat. No.    | Type         | Cover Color | Std. Pk. | Cat. No.                   | Type         | Cover Color | Std. Pk. |
| <input type="checkbox"/> | Enclosure - low cover  | 66 mm (2.60 in) | 105-404     | PS 1111-7-m  | gray        | 3        | 127-404                    | PC 1111-7-m  | gray        | 3        |
| <input type="checkbox"/> | Enclosure - high cover | 90 mm (3.54 in) | 105-904     | PS 1111-9-m  | gray        | 3        | 127-904                    | PC 1111-9-m  | gray        | 3        |
| <input type="checkbox"/> | Enclosure - low cover  | 66 mm (2.60 in) | 106-004     | PS 1111-7-tm | trans.      | 3        | 137-004                    | PC 1111-7-tm | trans.      | 3        |
| <input type="checkbox"/> | Enclosure - high cover | 90 mm (3.54 in) | 106-504     | PS 1111-9-tm | trans.      | 3        | 137-504                    | PC 1111-9-tm | trans.      | 3        |

## Accessories

| Ordering Information | Cat. No. | Type     | Std. Pk. |
|----------------------|----------|----------|----------|
| Mounting Plate       | 195-004  | MP1111   | 1        |
| DIN Rail TS35-81mm   | 198-081  | TS 35/81 | 1        |
| DIN Rail TS15-92mm   | 197-092  | TS 15/92 | 1        |
| Hinge Kit Set        | 190-002  | HK1      | 1        |
| Mounting Tab Kit     | 194-001  | MT1      | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



## TK 1309 – Polystyrene and Polycarbonate – 130x94mm (5.12x3.70in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

| Ordering Information |                        | Height mm (in)  | Polystyrene |              |             |          | Polycarbonate <sup>1</sup> |              |             |          |
|----------------------|------------------------|-----------------|-------------|--------------|-------------|----------|----------------------------|--------------|-------------|----------|
|                      |                        |                 | Cat. No.    | Type         | Cover Color | Std. Pk. | Cat. No.                   | Type         | Cover Color | Std. Pk. |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 110-409     | PS 1309-6-o  | gray        | 3        | 120-409                    | PC 1309-6-o  | gray        | 3        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 110-909     | PS 1309-8-o  | gray        | 3        | 120-909                    | PC 1309-8-o  | gray        | 3        |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 111-009     | PS 1309-6-to | trans.      | 3        | 130-009                    | PC 1309-6-to | trans.      | 3        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 111-509     | PS 1309-8-to | trans.      | 3        | 130-509                    | PC 1309-8-to | trans.      | 3        |

### Sidewalls with Metric Knockouts


| Ordering Information |                        | Height mm (in)  | Polystyrene |              |             |          | Polycarbonate <sup>1</sup> |              |             |          |
|----------------------|------------------------|-----------------|-------------|--------------|-------------|----------|----------------------------|--------------|-------------|----------|
|                      |                        |                 | Cat. No.    | Type         | Cover Color | Std. Pk. | Cat. No.                   | Type         | Cover Color | Std. Pk. |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 105-409     | PS 1309-6-m  | gray        | 3        | 127-409                    | PC 1309-6-m  | gray        | 3        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 105-909     | PS 1309-8-m  | gray        | 3        | 127-909                    | PC 1309-8-m  | gray        | 3        |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 106-009     | PS 1309-6-tm | trans.      | 3        | 137-009                    | PC 1309-6-tm | trans.      | 3        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 106-509     | PS 1309-8-tm | trans.      | 3        | 137-509                    | PC 1309-8-tm | trans.      | 3        |

### Accessories

| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-009  | MP1309    | 1        |
| DIN Rail TS35-106mm  | 198-106  | TS 35/106 | 1        |
| DIN Rail TS15-111mm  | 197-111  | TS 15/111 | 1        |
| Hinge Kit Set        | 190-002  | HK1       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



# TK 1313 – Polystyrene and Polycarbonate – 130x130mm (5.12x5.12in.)

## Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



## Smooth Sidewalls

| Ordering Information     |                        | Height mm (in)  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|--------------------------|------------------------|-----------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
|                          |                        |                 | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| <input type="checkbox"/> | Enclosure - low cover  | 75 mm (2.95 in) | 110-405     | PS 1313-7-o   | gray        | 2        | 120-405                    | PC 1313-7-o   | gray        | 2        |
| <input type="checkbox"/> | Enclosure - high cover | 99 mm (3.90 in) | 110-905     | PS 1313-10-o  | gray        | 2        | 120-905                    | PC 1313-10-o  | gray        | 2        |
| <input type="checkbox"/> | Enclosure - low cover  | 75 mm (2.95 in) | 111-005     | PS 1313-7-to  | trans.      | 2        | 130-005                    | PC 1313-7-to  | trans.      | 2        |
| <input type="checkbox"/> | Enclosure - high cover | 99 mm (3.90 in) | 111-505     | PS 1313-10-to | trans.      | 2        | 130-505                    | PC 1313-10-to | trans.      | 2        |

## Sidewalls with Metric Knockouts


| Ordering Information     |                        | Height mm (in)  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|--------------------------|------------------------|-----------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
|                          |                        |                 | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| <input type="checkbox"/> | Enclosure - low cover  | 75 mm (2.95 in) | 105-405     | PS 1313-7-m   | gray        | 2        | 127-405                    | PC 1313-7-m   | gray        | 2        |
| <input type="checkbox"/> | Enclosure - high cover | 99 mm (3.90 in) | 105-905     | PS 1313-10-m  | gray        | 2        | 127-905                    | PC 1313-10-m  | gray        | 2        |
| <input type="checkbox"/> | Enclosure - low cover  | 75 mm (2.95 in) | 106-005     | PS 1313-7-tm  | trans.      | 2        | 137-005                    | PC 1313-7-tm  | trans.      | 2        |
| <input type="checkbox"/> | Enclosure - high cover | 99 mm (3.90 in) | 106-505     | PS 1313-10-tm | trans.      | 2        | 137-505                    | PC 1313-10-tm | trans.      | 2        |

## Accessories


| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-005  | MP1313    | 1        |
| DIN Rail TS35-106mm  | 198-106  | TS 35/106 | 1        |
| DIN Rail TS15-111mm  | 197-111  | TS 15/111 | 1        |
| Hinge Kit Set        | 190-002  | HK1       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |

Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions



## Knockout Positions



## TK 1809 – Polystyrene and Polycarbonate – 180x94mm (7.09x3.70in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

| Ordering Information |                        | Height mm (in)  | Polystyrene |              |             |          | Polycarbonate <sup>1</sup> |              |             |          |
|----------------------|------------------------|-----------------|-------------|--------------|-------------|----------|----------------------------|--------------|-------------|----------|
|                      |                        |                 | Cat. No.    | Type         | Cover Color | Std. Pk. | Cat. No.                   | Type         | Cover Color | Std. Pk. |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 110-410     | PS 1809-6-o  | gray        | 2        | 120-410                    | PC 1809-6-o  | gray        | 2        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 110-910     | PS 1809-8-o  | gray        | 2        | 120-910                    | PC 1809-8-o  | gray        | 2        |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 111-010     | PS 1809-6-to | trans.      | 2        | 130-010                    | PC 1809-6-to | trans.      | 2        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 111-510     | PS 1809-8-to | trans.      | 2        | 130-510                    | PC 1809-8-to | trans.      | 2        |

### Sidewalls with Metric Knockouts


| Ordering Information |                        | Height mm (in)  | Polystyrene |              |             |          | Polycarbonate <sup>1</sup> |              |             |          |
|----------------------|------------------------|-----------------|-------------|--------------|-------------|----------|----------------------------|--------------|-------------|----------|
|                      |                        |                 | Cat. No.    | Type         | Cover Color | Std. Pk. | Cat. No.                   | Type         | Cover Color | Std. Pk. |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 105-410     | PS 1809-6-m  | gray        | 2        | 127-410                    | PC 1809-6-m  | gray        | 2        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 105-910     | PS 1809-8-m  | gray        | 2        | 127-910                    | PC 1809-8-m  | gray        | 2        |
|                      | Enclosure - low cover  | 57 mm (2.24 in) | 106-010     | PS 1809-6-tm | trans.      | 2        | 137-010                    | PC 1809-6-tm | trans.      | 2        |
|                      | Enclosure - high cover | 81 mm (3.19 in) | 106-510     | PS 1809-8-tm | trans.      | 2        | 137-510                    | PC 1809-8-tm | trans.      | 2        |

### Accessories

| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-010  | MP1809    | 1        |
| DIN Rail TS35-144mm  | 198-144  | TS 35/144 | 1        |
| DIN Rail TS15-154mm  | 197-154  | TS 15/154 | 1        |
| Hinge Kit Set        | 190-002  | HK1       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A




Side B



# TK 1811 – Polystyrene and Polycarbonate – 180x110mm (7.09x4.33in.)

## Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



## Smooth Sidewalls

|                           |                  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|---------------------------|------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
| Ordering Information      | Height mm (in)   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover     | 90 mm (3.54 in)  | 110-406     | PS 1811-9-o   | gray        | 2        | 120-406                    | PC 1811-9-o   | gray        | 2        |
| Enclosure - high cover    | 111 mm (4.37 in) | 110-906     | PS 1811-11-o  | gray        | 2        | 120-906                    | PC 1811-11-o  | gray        | 2        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 109-406     | PS 1811-16-o  | gray        | 2        | 121-406                    | PC 1811-16-o  | gray        | 2        |
| Enclosure - low cover     | 90 mm (3.54 in)  | 111-006     | PS 1811-9-to  | trans.      | 2        | 130-006                    | PC 1811-9-to  | trans.      | 2        |
| Enclosure - high cover    | 111 mm (4.37 in) | 111-506     | PS 1811-11-to | trans.      | 2        | 130-506                    | PC 1811-11-to | trans.      | 2        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 112-006     | PS 1811-16-to | trans.      | 2        | 131-006                    | PC 1811-16-to | trans.      | 2        |

## Sidewalls with Metric Knockouts


|                           |                  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|---------------------------|------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
| Ordering Information      | Height mm (in)   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover     | 90 mm (3.54 in)  | 105-406     | PS 1811-9-m   | gray        | 2        | 127-406                    | PC 1811-9-m   | gray        | 2        |
| Enclosure - high cover    | 111 mm (4.37 in) | 105-906     | PS 1811-11-m  | gray        | 2        | 127-906                    | PC 1811-11-m  | gray        | 2        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 104-406     | PS 1811-16-m  | gray        | 2        | 128-406                    | PC 1811-16-m  | gray        | 2        |
| Enclosure - low cover     | 90 mm (3.54 in)  | 106-006     | PS 1811-9-tm  | trans.      | 2        | 137-006                    | PC 1811-9-tm  | trans.      | 2        |
| Enclosure - high cover    | 111 mm (4.37 in) | 106-506     | PS 1811-11-tm | trans.      | 2        | 137-506                    | PC 1811-11-tm | trans.      | 2        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 107-006     | PS 1811-16-tm | trans.      | 2        | 138-006                    | PC 1811-16-tm | trans.      | 2        |

## Accessories

| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-006  | MP1811    | 1        |
| DIN Rail TS35-144mm  | 198-144  | TS 35/144 | 1        |
| Hinge Kit Set        | 190-005  | HK2       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



## TK 1818f – Polystyrene and Polycarbonate – 182x180mm (7.17x7.09in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

|                           |                  | Polystyrene |                |             |          |  | Polycarbonate <sup>1</sup> |                |             |          |
|---------------------------|------------------|-------------|----------------|-------------|----------|--|----------------------------|----------------|-------------|----------|
| Ordering Information      | Height mm (in)   | Cat. No.    | Type           | Cover Color | Std. Pk. |  | Cat. No.                   | Type           | Cover Color | Std. Pk. |
| Enclosure - low cover     | 63 mm (2.48 in)  | 110-413     | PS 1818-6f-o   | gray        | 2        |  | 120-413                    | PC 1818-6f-o   | gray        | 2        |
| Enclosure - high cover    | 84 mm (3.31 in)  | 110-913     | PS 1818-8f-o   | gray        | 2        |  | 120-913                    | PC 1818-8f-o   | gray        | 2        |
| Enclosure - top hat cover | 137 mm (5.39 in) | 109-413     | PS 1818-13f-o  | gray        | 1        |  | 121-413                    | PC 1818-13f-o  | gray        | 1        |
| Enclosure - low cover     | 63 mm (2.48 in)  | 111-013     | PS 1818-6f-to  | trans.      | 2        |  | 130-013                    | PC 1818-6f-to  | trans.      | 2        |
| Enclosure - high cover    | 84 mm (3.31 in)  | 111-513     | PS 1818-8f-to  | trans.      | 2        |  | 130-513                    | PC 1818-8f-to  | trans.      | 2        |
| Enclosure - top hat cover | 137 mm (5.39 in) | 112-013     | PS 1818-13f-to | trans.      | 1        |  | 131-013                    | PC 1818-13f-to | trans.      | 1        |

### Sidewalls with Metric Knockouts


|                           |                  | Polystyrene |                |             |          |  | Polycarbonate <sup>1</sup> |                |             |          |
|---------------------------|------------------|-------------|----------------|-------------|----------|--|----------------------------|----------------|-------------|----------|
| Ordering Information      | Height mm (in)   | Cat. No.    | Type           | Cover Color | Std. Pk. |  | Cat. No.                   | Type           | Cover Color | Std. Pk. |
| Enclosure - low cover     | 63 mm (2.48 in)  | 105-413     | PS 1818-6f-m   | gray        | 2        |  | 127-413                    | PC 1818-6f-m   | gray        | 2        |
| Enclosure - high cover    | 84 mm (3.31 in)  | 105-913     | PS 1818-8f-m   | gray        | 2        |  | 127-913                    | PC 1818-8f-m   | gray        | 2        |
| Enclosure - top hat cover | 137 mm (5.39 in) | 104-413     | PS 1818-13f-m  | gray        | 1        |  | 128-413                    | PC 1818-13f-m  | gray        | 1        |
| Enclosure - low cover     | 63 mm (2.48 in)  | 106-013     | PS 1818-6f-tm  | trans.      | 2        |  | 137-013                    | PC 1818-6f-tm  | trans.      | 2        |
| Enclosure - high cover    | 84 mm (3.31 in)  | 106-513     | PS 1818-8f-tm  | trans.      | 2        |  | 137-513                    | PC 1818-8f-tm  | trans.      | 2        |
| Enclosure - top hat cover | 137 mm (5.39 in) | 107-013     | PS 1818-13f-tm | trans.      | 1        |  | 138-013                    | PC 1818-13f-tm | trans.      | 1        |

### Accessories


| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-007  | MP1818    | 1        |
| DIN Rail TS35-144mm  | 198-144  | TS 35/144 | 1        |
| Hinge Kit Set        | 190-005  | HK2       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |

Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions



## Knockout Positions



## TK 1818 – Polystyrene and Polycarbonate – 182x180mm (7.17x7.09in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

| Ordering Information      |  | Height<br>mm (in) | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|---------------------------|--|-------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
|                           |  |                   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover     |  | 90 mm (3.54 in)   | 110-407     | PS 1818-9-o   | gray        | 2        | 120-407                    | PC 1818-9-o   | gray        | 2        |
| Enclosure - high cover    |  | 111 mm (4.37 in)  | 110-907     | PS 1818-11-o  | gray        | 2        | 120-907                    | PC 1818-11-o  | gray        | 2        |
| Enclosure - top hat cover |  | 165 mm (6.50 in)  | 109-407     | PS 1818-16-o  | gray        | 1        | 121-407                    | PC 1818-16-o  | gray        | 1        |
| Enclosure - low cover     |  | 90 mm (3.54 in)   | 111-007     | PS 1818-9-to  | trans.      | 2        | 130-007                    | PC 1818-9-to  | trans.      | 2        |
| Enclosure - high cover    |  | 111 mm (4.37 in)  | 111-507     | PS 1818-11-to | trans.      | 2        | 130-507                    | PC 1818-11-to | trans.      | 2        |
| Enclosure - top hat cover |  | 165 mm (6.50 in)  | 112-007     | PS 1818-16-to | trans.      | 1        | 131-007                    | PC 1818-16-to | trans.      | 1        |

### Sidewalls with Metric Knockouts


| Ordering Information      |  | Height<br>mm (in) | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|---------------------------|--|-------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
|                           |  |                   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover     |  | 90 mm (3.54 in)   | 105-407     | PS 1818-9-m   | gray        | 2        | 127-407                    | PC 1818-9-m   | gray        | 2        |
| Enclosure - high cover    |  | 111 mm (4.37 in)  | 105-907     | PS 1818-11-m  | gray        | 2        | 127-907                    | PC 1818-11-m  | gray        | 2        |
| Enclosure - top hat cover |  | 165 mm (6.50 in)  | 104-407     | PS 1818-16-m  | gray        | 1        | 128-407                    | PC 1818-16-m  | gray        | 1        |
| Enclosure - low cover     |  | 90 mm (3.54 in)   | 106-007     | PS 1818-9-tm  | trans.      | 2        | 137-007                    | PC 1818-9-tm  | trans.      | 2        |
| Enclosure - high cover    |  | 111 mm (4.37 in)  | 106-507     | PS 1818-11-tm | trans.      | 2        | 137-507                    | PC 1818-11-tm | trans.      | 2        |
| Enclosure - top hat cover |  | 165 mm (6.50 in)  | 107-007     | PS 1818-16-tm | trans.      | 1        | 138-007                    | PC 1818-16-tm | trans.      | 1        |

### Accessories

| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-007  | MP1818    | 1        |
| DIN Rail TS35-144mm  | 198-144  | TS 35/144 | 1        |
| Hinge Kit Set        | 190-005  | HK2       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



## TK 2518f – Polystyrene and Polycarbonate – 254x180mm (10.0x7.09in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

| Smooth Sidewalls                                                                  |                           |                  | Polystyrene |                |             |          | Polycarbonate <sup>1</sup> |                |             |          |
|-----------------------------------------------------------------------------------|---------------------------|------------------|-------------|----------------|-------------|----------|----------------------------|----------------|-------------|----------|
| Ordering Information                                                              |                           | Height mm (in)   | Cat. No.    | Type           | Cover Color | Std. Pk. | Cat. No.                   | Type           | Cover Color | Std. Pk. |
|  | Enclosure - low cover     | 63 mm (2.48 in)  | 110-411     | PS 2518-6f-o   | gray        | 1        | 120-411                    | PC 2518-6f-o   | gray        | 1        |
|  | Enclosure - high cover    | 84 mm (3.31 in)  | 110-911     | PS 2518-8f-o   | gray        | 1        | 120-911                    | PC 2518-8f-o   | gray        | 1        |
|  | Enclosure - top hat cover | 137 mm (5.39 in) | 109-411     | PS 2518-14f-o  | gray        | 1        | 121-411                    | PC 2518-14f-o  | gray        | 1        |
|  | Enclosure - low cover     | 63 mm (2.48 in)  | 111-011     | PS 2518-6f-to  | trans.      | 1        | 130-011                    | PC 2518-6f-to  | trans.      | 1        |
|  | Enclosure - high cover    | 84 mm (3.31 in)  | 111-511     | PS 2518-8f-to  | trans.      | 1        | 130-511                    | PC 2518-8f-to  | trans.      | 1        |
|  | Enclosure - top hat cover | 137 mm (5.39 in) | 112-011     | PS 2518-14f-to | trans.      | 1        | 131-011                    | PC 2518-14f-to | trans.      | 1        |

### Sidewalls with Metric Knockouts


| Sidewalls with Metric Knockouts                                                     |                           |                   | Polystyrene |                |                |             | Polycarbonate <sup>1</sup> |                |                |             |
|-------------------------------------------------------------------------------------|---------------------------|-------------------|-------------|----------------|----------------|-------------|----------------------------|----------------|----------------|-------------|
| Ordering Information                                                                |                           | Height<br>mm (in) | Cat. No.    | Type           | Cover<br>Color | Std.<br>Pk. | Cat. No.                   | Type           | Cover<br>Color | Std.<br>Pk. |
|  | Enclosure - low cover     | 63 mm (2.48 in)   | 105-411     | PS 2518-6f-m   | gray           | 1           | 127-411                    | PC 2518-6f-m   | gray           | 1           |
|  | Enclosure - high cover    | 84 mm (3.31 in)   | 105-911     | PS 2518-8f-m   | gray           | 1           | 127-911                    | PC 2518-8f-m   | gray           | 1           |
|  | Enclosure - top hat cover | 137 mm (5.39 in)  | 104-411     | PS 2518-14f-m  | gray           | 1           | 128-411                    | PC 2518-14f-m  | gray           | 1           |
|  | Enclosure - low cover     | 63 mm (2.48 in)   | 106-011     | PS 2518-6f-tm  | trans.         | 1           | 137-011                    | PC 2518-6f-tm  | trans.         | 1           |
|  | Enclosure - high cover    | 84 mm (3.31 in)   | 106-511     | PS 2518-8f-tm  | trans.         | 1           | 137-511                    | PC 2518-8f-tm  | trans.         | 1           |
|  | Enclosure - top hat cover | 137 mm (5.39 in)  | 107-011     | PS 2518-14f-tm | trans.         | 1           | 138-011                    | PC 2518-14f-tm | trans.         | 1           |

### Accessories

| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-008  | MP2518    | 1        |
| DIN Rail TS35-216mm  | 198-216  | TS 35/216 | 1        |
| Hinge Kit Set        | 190-005  | HK2       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



## TK 2518 – Polystyrene and Polycarbonate – 254x180mm (10.0x7.09in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

|                           |                  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|---------------------------|------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
| Ordering Information      | Height mm (in)   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover     | 90 mm (3.54 in)  | 110-408     | PS 2518-9-o   | gray        | 1        | 120-408                    | PC 2518-9-o   | gray        | 1        |
| Enclosure - high cover    | 111 mm (4.37 in) | 110-908     | PS 2518-11-o  | gray        | 1        | 120-908                    | PC 2518-11-o  | gray        | 1        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 109-408     | PS 2518-16-o  | gray        | 1        | 121-408                    | PC 2518-16-o  | gray        | 1        |
| Enclosure - low cover     | 90 mm (3.54 in)  | 111-008     | PS 2518-9-to  | trans.      | 1        | 130-008                    | PC 2518-9-to  | trans.      | 1        |
| Enclosure - high cover    | 111 mm (4.37 in) | 111-508     | PS 2518-11-to | trans.      | 1        | 130-508                    | PC 2518-11-to | trans.      | 1        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 112-008     | PS 2518-16-to | trans.      | 1        | 131-008                    | PC 2518-16-to | trans.      | 1        |

### Sidewalls with Metric Knockouts


|                           |                  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|---------------------------|------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
| Ordering Information      | Height mm (in)   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover     | 90 mm (3.54 in)  | 105-408     | PS 2518-9-m   | gray        | 1        | 127-408                    | PC 2518-9-m   | gray        | 1        |
| Enclosure - high cover    | 111 mm (4.37 in) | 105-908     | PS 2518-11-m  | gray        | 1        | 127-908                    | PC 2518-11-m  | gray        | 1        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 104-408     | PS 2518-16-m  | gray        | 1        | 128-408                    | PC 2518-16-m  | gray        | 1        |
| Enclosure - low cover     | 90 mm (3.54 in)  | 106-008     | PS 2518-9-tm  | trans.      | 1        | 137-008                    | PC 2518-9-tm  | trans.      | 1        |
| Enclosure - high cover    | 111 mm (4.37 in) | 106-508     | PS 2518-11-tm | trans.      | 1        | 137-508                    | PC 2518-11-tm | trans.      | 1        |
| Enclosure - top hat cover | 165 mm (6.50 in) | 107-008     | PS 2518-16-tm | trans.      | 1        | 138-008                    | PC 2518-16-tm | trans.      | 1        |

### Accessories

| Ordering Information | Cat. No. | Type      | Std. Pk. |
|----------------------|----------|-----------|----------|
| Mounting Plate       | 195-008  | MP2518    | 1        |
| DIN Rail TS35-216mm  | 198-216  | TS 35/216 | 1        |
| Hinge Kit Set        | 190-005  | HK2       | 1        |
| Mounting Tab Kit     | 194-001  | MT1       | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions




## Knockout Positions

Side A



Side B



## TK 3625 – Polystyrene and Polycarbonate – 360x254mm (14.2x10.0in.)

### Standard Features

- **Protection Level:** IP66 (NEMA Type: 4X with gray cover, 12K with transparent cover)
- **Technical:** Smooth or Knockout Sidewalls  
Gray or Tinted Transparent Cover  
Multiple Enclosure Mounting Options
- **Enclosure Material:** Polystyrene or Polycarbonate
- **Gasket Material:** Polyurethane
- **Color:** Light Gray
- **Temperature Range:** Polystyrene  
-40°C to 70°C (-40°F to 158°F)  
Polycarbonate  
-35°C to 120°C (-31°F to 248°F)
- **Accessories:** See section below



### Smooth Sidewalls

|                        |                  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|------------------------|------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
| Ordering Information   | Height mm (in)   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover  | 111 mm (4.37 in) | 110-412     | PS 3625-11-o  | gray        | 1        | 120-412                    | PC 3625-11-o  | gray        | 1        |
| Enclosure - high cover | 165 mm (6.50 in) | 110-912     | PS 3625-16-o  | gray        | 1        | 120-912                    | PC 3625-16-o  | gray        | 1        |
| Enclosure - low cover  | 111 mm (4.37 in) | 111-012     | PS 3625-11-to | trans.      | 1        | 130-012                    | PC 3625-11-to | trans.      | 1        |
| Enclosure - high cover | 165 mm (6.50 in) | 111-512     | PS 3625-16-to | trans.      | 1        | 130-512                    | PC 3625-16-to | trans.      | 1        |

### Sidewalls with Metric Knockouts


|                        |                  | Polystyrene |               |             |          | Polycarbonate <sup>1</sup> |               |             |          |
|------------------------|------------------|-------------|---------------|-------------|----------|----------------------------|---------------|-------------|----------|
| Ordering Information   | Height mm (in)   | Cat. No.    | Type          | Cover Color | Std. Pk. | Cat. No.                   | Type          | Cover Color | Std. Pk. |
| Enclosure - low cover  | 111 mm (4.37 in) | 105-412     | PS 3625-11-m  | gray        | 1        | 127-412                    | PC 3625-11-m  | gray        | 1        |
| Enclosure - high cover | 165 mm (6.50 in) | 105-912     | PS 3625-16-m  | gray        | 1        | 127-912                    | PC 3625-16-m  | gray        | 1        |
| Enclosure - low cover  | 111 mm (4.37 in) | 106-012     | PS 3625-11-tm | trans.      | 1        | 137-012                    | PC 3625-11-tm | trans.      | 1        |
| Enclosure - high cover | 165 mm (6.50 in) | 106-512     | PS 3625-16-tm | trans.      | 1        | 137-512                    | PC 3625-16-tm | trans.      | 1        |

### Accessories

| Ordering Information | Cat. No. | Type       | Std. Pk. |
|----------------------|----------|------------|----------|
| Mounting Plate       | 195-012  | MP3625     | 1        |
| DIN Rail TS35-336mm  | 198-336  | TS 35/ 336 | 1        |
| Hinge Kit Set        | 190-005  | HK2        | 1        |
| Mounting Tab Kit     | 194-001  | MT1        | 1        |


Please refer to pages 116-120 for additional accessories and detailed information.

## Dimensions



## Knockout Positions

Side A



Side B

