

## Split Wrap Braided Sleeving

A bundling and protection option with a lateral split and a semi-rigid braid configuration that is the ideal solution for circumstances where ease of installation is the primary concern. The lateral split allows the sleeving to open up to adjust to the bundling requirement while the 25% edge overlap folds back over the connector or splices.



### Application

More flexible than spiral wraps or convoluted tubing, this product is a fast and easy option for adding protection in post-assembly or post-installation situations.

### Benefits

- Needs no fasteners (i.e., tape, hook and loop, etc.).
- Bends to a tight radius without distortion or splitting open.
- Allows future access without disassembly.
- Withstands cuts, abrasions and tension.

#### Material Data

|                       |                                  |
|-----------------------|----------------------------------|
| Material              | PET (Polyester)                  |
| Flammability          | UL 94-V0                         |
| Operating Temperature | -94°F to 257°F<br>-70°C to 125°C |
| Melt Point            | 482°F / 250°C                    |
| Abrasion Protection   | Medium                           |
| Recommended Cutting   | Hot Knife                        |



#### Product Selection

| Part No.                      | Nominal Size |       | Type        | Wall Thickness |     | Color | Reel Length* |         | Weight |     |
|-------------------------------|--------------|-------|-------------|----------------|-----|-------|--------------|---------|--------|-----|
|                               | in.          | mm.   |             | in.            | mm. |       | ft.          | m.      | lbs.   | kg. |
| 170-03037                     | 1/4          | 6.4   | BSPSW140    | .025           | .64 | Black | 100          | 30.5    | .60    | .27 |
| 170-03024                     | 1/2          | 12.7  | BSPSW120    | .025           | .64 | Black | 75           | 22.9    | 1.05   | .48 |
| 170-03038                     | 3/4          | 19.1  | BSPSW340    | .025           | .64 | Black | 50           | 15.2    | .80    | .36 |
| 170-03025                     | 1            | 25.4  | BSPSW100    | .038           | .97 | Black | 50           | 15.2    | 1.0    | .45 |
| 170-03026                     | 1-1/4        | 31.8  | BSPSW1140   | .038           | .97 | Black | 25           | 7.1     | .60    | .27 |
| <b>Bulk Box</b>               |              |       |             |                |     |       |              |         |        |     |
| 170-03124                     | 1/8          | 3.2   | BSPSW180B   | .024           | .61 | Black | 400          | 121.9   | .80    | .36 |
| 170-03125                     | 1/4          | 6.4   | BSPSW140B   | .025           | .64 | Black | 200          | 61.0    | 1.2    | .54 |
| 170-03126                     | 1/2          | 12.7  | BSPSW120B   | .025           | .64 | Black | 150          | 45.7    | 2.1    | .95 |
| 170-03127                     | 3/4          | 19.1  | BSPSW340B   | .025           | .64 | Black | 100          | 30.5    | 1.6    | .73 |
| 170-03128                     | 1            | 25.4  | BSPSW100B   | .038           | .97 | Black | 100          | 30.5    | 2.0    | .91 |
| 170-03129                     | 1-1/4        | 31.8  | BSPSW1140B  | .038           | .97 | Black | 75           | 22.9    | 1.8    | .82 |
| 170-03130                     | 1-1/2        | 38.1  | BSPSW1120B  | .038           | .97 | Black | 75           | 22.9    | 2.1    | .95 |
| 170-03131                     | 2            | 50.8  | BSPSW200B   | .038           | .97 | Black | 50           | 15.2    | 1.8    | .82 |
| <b>Large Bulk Sized Reels</b> |              |       |             |                |     |       |              |         |        |     |
| 170-03132                     | 1/8          | 3.2   | BSPSW180LB  | .024           | .61 | Black | 10,000       | 3,048.8 | 20.0   | 9.0 |
| 170-03133                     | 1/4          | 6.4   | BSPSW140LB  | .025           | .64 | Black | 3,000        | 914.4   | 18.0   | 8.2 |
| 170-03134                     | 1/2          | 12.7  | BSPSW120LB  | .025           | .64 | Black | 1,200        | 365.8   | 12.0   | 5.4 |
| 170-03135                     | 3/4          | 19.05 | BSPSW340LB  | .025           | .64 | Black | 500          | 152.4   | 16.8   | 7.6 |
| 170-03136                     | 1            | 25.4  | BSPSW100LB  | .038           | .97 | Black | 400          | 121.9   | 8.0    | 3.6 |
| 170-03137                     | 1-1/4        | 31.8  | BSPSW140LB  | .038           | .97 | Black | 300          | 91.4    | 8.0    | 3.6 |
| 170-03138                     | 1-1/2        | 38.1  | BSPSW1120LB | .038           | .97 | Black | 200          | 61.0    | 7.2    | 3.3 |
| 170-03139                     | 2            | 50.8  | BSPSW200LB  | .038           | .97 | Black | 150          | 45.7    | 5.4    | 2.4 |

Use Part No. for ordering and Type for specification. \*Additional sizes available upon request.