

**190-00302**

Snapper Hose Clamps, .714"/.81" Min/Max Diameter, POM, White, 100/pkg

Article Number: 190-00302

Part Number: 190-00302

Type: SNP14A

→ Find a Distributor

→ Order Samples

➔Get Technical Drawings



→ **Base Data**

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part No.            | 190-00302                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Type                | SNP14A                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Color               | White (WH)                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Features            | <ul style="list-style-type: none"><li>• Designed for quick, ratcheted installation and can be released and reused.</li><li>• Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.</li></ul>                                                                                                                                                                                          |
| Typical Application | <p>Snapper hose clamps are used in a variety of markets and diverse applications.</p> <ul style="list-style-type: none"><li>• Automotive</li><li>• Air Lines</li><li>• Pumps</li><li>• Marine</li><li>• Drain Lines</li><li>• Sprayers</li><li>• Truck</li><li>• Water Lines</li><li>• Fuel Lines</li><li>• Heavy Equipment</li><li>• Sprinkler Systems</li><li>• Garden Hoses</li><li>• Many more hose and tubing applications</li></ul> |
| Variant             | Closed                                                                                                                                                                                                                                                                                                                                                                                                                                    |

### → Product Dimensions

|                     |                  |
|---------------------|------------------|
| Width (W) min.      | 0.805" / 20.45mm |
| Width (W) max.      | 1.157" / 29.39mm |
| Width (W2)          | .233" / 5.92mm   |
| Min. Ø              | 0.714" / 18.14mm |
| Max. Ø              | 0.81" / 20.57mm  |
| Wall Thickness (WT) | .069 "           |
| Wall Thickness      | 1.75mm           |

## ➔ Material and Specifications

|                       |                                                                                     |
|-----------------------|-------------------------------------------------------------------------------------|
| Material              | Polyacetal (POM)                                                                    |
| Flammability          | UL94 HB                                                                             |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C)                                                |
| ROHS Conformity       |  |

## → Logistic and Packaging

|                       |     |
|-----------------------|-----|
| <b>Packaging Type</b> | bag |
|-----------------------|-----|