




SPECIFICATIONS:

MATERIAL:-

HOUSING: BLACK PA9T (UL94V-0)

PLUNGER & BARREL: BRASS

SPRING: SUS 304

FINISH:-

CONTACT SURFACE: TIN/GOLD OVER NICKEL UNDERPLATE

ELECTRICAL:-

CURRENT RATING: 1 AMP

WORKING VOLTAGE: DC 12 V

CONTACT RESISTANCE: 50 mΩ MAX AT WORKING HT

MECHANICAL:-

DURABILITY: 10 000 CYCLES MINIMUM

UNLOADED HT: 4.2mm

WORKING HT: 3.4mm

SPRING FORCE: 120g ±20% AT WORKING HT

TOLERANCE:

DIMENSIONS	ANGLES
X. = ±0.25mm	±2.0°
X.X = ±0.15mm	±1.0°
X.XX = ±0.10mm	±0.5°

NOTES: ALL DIMENSIONS AND NOTES
MARKED ✖ ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. Q1-02A

NAME	ISS.	DATE	C/NOTE
Allan	1	01.08.06	-
APPROVED: <i>Ben</i>			
CHECKED:			
DRAWN: Allan			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH:

SEE NOTES

S/AREA:

mm²

TITLE:

PITCH 2.5mm HEIGHT 4.2mm
3-POS POGO PIN CONNECTOR

DRAWING NUMBER:

P20-0345R

SHT
1
OF
1