



Ty-Rap®

T&B Catalog Number: TY533M
UPC Number: 78621082550
Description: Cable Tie 18lb 4" Natural Nylon with Stainless Steel Locking Device #4 Mounting Hole
Status: Active

General

Material	Nylon 6.6
Color	Natural
Mounting Hole Size	#4

Dimension Information

Length (inches)	4
Width (inches)	.091
Max. Wire Bundle Diameter (inches)	.625

Specifications

Tensile Strength (lbs.)	18
Temperature Rating	-40°F to 185°F
Flamability Rating	UL 94 V-2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	0.12 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website


Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications




Ty-Rap® Cable Ties




TY533M



TY534M




TY535M
TY5354M




TY537M

• Great for use with screws, nuts and bolts for secure fastening to surfaces.



TY554M



TY538M




TY533MX



TY534MX



TY535MX
TY5354MX



TY537MX

The MX series cable ties are recommended for outdoor use. The addition of carbon black provides good ultraviolet resistance and prolongs the useful life of the cable tie.

Ty-Rap® Mounting Head Cable Ties

Std. Cat. No.	Bulk Cat. No.	Body Width (in.)	Length (in.)	Max. Wire Bundle Dia. (in.)	Mounting Hole	Tensile Strength (lbs.)	Std. Pkg.	Bulk Pkg.
TY533M	TY33M	.091	4.00	.625	#4	18	100	1000
TY534M	TY34M	.140	6.00	1.125	#8	40	100	1000
TY535M	TY35M	.184	7.80	1.750	#10	50	100	1000
TY5354M	TY354M	.184	14.60	4.000	#10	50	100	1000
TY1435M	—	.189	7.8	1.77	.248	50	—	1000
TY635M	—	.189	7.8	1.77	.138	50	—	1000
TYF535M	TYF35M	.189	7.24	1.77	.138	50	100	1000
TY537M	TY37M	.301	13.90	3.500	¼	120	50	500

Cable ties made from natural nylon 6/6 are excellent performers in most applications. Nylon 6/6 is recommended for use in temperatures ranging from 185°F to -40°F.



Ty-Rap® Push Mount Cable Ties

For use in 3/16" and 1/4" pre-drilled holes. Thickness panel .094 max. (TY554M) Range .04 - .156 (TY538M)

Std. Cat. No.	Bulk Cat. No.	Body Width (in.)	Length (in.)	Max. Wire Bundle Dia. (in.)	Mounting Hole	Tensile Strength (lbs.)	Std. Pkg.	Bulk Pkg.
TY554M	TY54M	.140	5.96	1.125	3/16	40	100	1000
TY538M	TY38M*	.184	7.80	1.750	¼	50	100	1000

Cable ties made from natural nylon 6/6 are excellent performers in most applications. Nylon 6/6 is recommended for use in temperatures ranging from 185°F to -40°F.

* Nylon 6/6 UV weather resistant version available (TY38MX).

Nylon 6/6 Weather Resistant

Std. Cat. No.	Bulk Cat. No.	Body Width (in.)	Length (in.)	Max. Wire Bundle Dia. (in.)	Mounting Hole	Tensile Strength (lbs.)	Std. Pkg.	Bulk Pkg.
TY533MX	TY33MX	.091	4.00	.625	#4	18	100	1000
TY534MX	TY34MX	.140	6.00	1.125	#8	40	100	1000
TY535MX	TY35MX	.184	7.80	1.750	#10	50	100	1000
TY5354MX	TY354MX	.184	14.60	4.000	#10	50	100	1000
TY538MX	TY38MX	.184	7.80	1.750	¼	50	—	1000
TY537MX	TY37MX	.301	13.90	3.500	¼	120	50	500



ULTRAVIOLET
RESISTANT

How to Order Color-Coded Ty-Rap® Ties and Accessories

Color	Suffix No.	Color	Suffix No.
Black (outdoor)	X	Green	5
Brown	1	Blue	6
Red	2	Purple	7
Orange	3	Gray	8
Yellow	4	White	9

Natural nylon is standard. For colored Ty-Rap® ties, add the following suffix numbers to catalog numbers. Example: TY25M-2 would be red TY25M. (Consult customer service for ordering information.)