







Termination Cover
(1 Places)Wire Holder
(2 Places)

FEATURES:

- Half pitch 1.27mm(.050") series
- Centronic type female connector for 1.27mm(.050") ribbon cable round cable
- Panel mount receptacle assemblies bracket with latch block and without latch block
- Die-Cast body provide EMI/RFI shielded

MATERIALS:

- Housing And Cover: Plastic thermoplastic P.B.T UL94V-0 black
- Contact: Phosphor bronze gold selective plated
- Bracketshell: Die-Cast zinc nickel plated over copper

ELECTRICAL:

- Current Rating: 1 Amp
- Insulation Resistance: 500MW/Min
- Withstanding Voltage: 500V AC/Min
- Contact Resistance: 35mW Max
- Temperature Range: -55°C ~ +105°C

SERIES

Flat cable IDC termination

NUMBER OF CONTACT:

CONTACT TYPES:

F = female

CONTACT PLATING:

- 0 = selective flash gold
- 1 = selective 15u" gold
- 2 = selective 30u" gold

FIXING DEVICE :


L : Latching + Jackscrews
S : jackscrews only

THREADED HOLES:



3 = M2,6

WIRE HOLDER:



- 6 = 0.62mm
- 7 = 0.75mm
- 9 = 0.9mm



L Type




S Type



Amphenol Socapex
Usine de Dole

ECH. ENS.
N SERIE



DOSSIER

DATE DU TIRAGE

DESIGNATION

MINI D SERIES

TOL. GEN.

VOLUME PIECE

SURFACE PIECE

PROTECTION

TRAITEMENT

MATIERE

CLIENT

MODIFICATIONS

EXEC.

DATE

Approb

IND.

N INTERNE

MD5 ID 26F

COMMUNICATION ET UTILISATION INTERDITES SAUF AUTORISATION