

PART
NAME

PLASTIBOX (STYLE A)

PART
No.



PT-11338 & PS-11339

MATERIAL: HIGH-IMPACT ABSCOLOR: BLACK OR GRAYFINISH: PREFIX PS - TEXTURED BODY WITH SMOOTH TOP INSERT.

PREFIX PT - TEXTURED BODY WITH TEXTURED TOP.

SIX (6) #4 x 0.375" LG. SCREWS
SUPPLIED FOR ASSEMBLING TOP.

FOUR (4) NON-SKID PUSH-ON FEET SUPPLIED.

*-USABLE AREA ON COVER ALSO
AVAILABLE FOR CUSTOM MOLDING.NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
UNLESS OTHERWISE SPECIFIED.0.260 DIA. BOSS WITH 0.093 DIA.
HOLE x 0.310 DEEP (16) PLACES
MOUNTING BOSSES USE EITHER M2.5 METRIC
OR #4 STD. SHEET METAL SCREWS
x 0.250" LG. (NOT SHOWN)PART
NAME



PLASTIBOX (STYLE B)

PART
No.

PSS-11350 & PNS-11351

MATERIAL: HIGH-IMPACT ABSCOLOR: BLACK OR GRAYFINISH: PREFIX PSS- TEXTURED BODY WITH SMOOTH
TOP AND END INSERTS.PREFIX PNS- TEXTURED BODY WITH SMOOTH
TOP AND END INSERTS AND 9V
BATTERY COMPARTMENT.SIX (6) #4 x 0.375" LG. SCREWS
SUPPLIED FOR ASSEMBLING TOP.

FOUR (4) NON-SKID PUSH-ON FEET SUPPLIED.

*-USABLE AREA ON COVER ALSO
AVAILABLE FOR CUSTOM MOLDING.0.260 DIA. BOSS WITH 0.093 DIA.
HOLE x 0.310 DEEP (16) PLACES
MOUNTING BOSSES USE EITHER M2.5 METRIC
OR #4 STD. SHEET METAL SCREWS
x 0.250" LG. (NOT SHOWN)NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
UNLESS OTHERWISE SPECIFIED.