





Specification:

Current rating: 1 A Max.
Dielectric withstanding voltage: 100 V(ac) for 1 min.
Contact resistance: 50 mW Max.
Insulation resistance: 100 M W Min.
Total mating force: 3.57 Kgf Max.
Total unmating force: 0.71 Kgf Min.
Temperature range: -0 'C~50 'C

Material:

Housing: P.B.T
Contact: Phosphor Bronze
Shell: SPCC.

玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.		UNIT	SCALE	PART NAME	
		MM	6: 1	MINI USB B TYPE 5P (MINI B SOLDER TYPE)	
制表日:2002/05/09	DRAWING.	APPD. CKD.	TOLERANCE	PART NO.	REV.
	Jane		± 0.3	C8320-05BMSSB0	A