

High Precision Mini Tweezers

Fine tips without the excess bulk of long tweezers



M-00D.SA
M-00D.S

3 1/2" 90mm
serrated tips and grips



M-2A.SA
M-2A.S

2 3/4" 70mm
rounded flat tips



M-3.SA
M-3.S

2 3/4" 70mm
sharp, fine tips



M-4.SA
M-4.S

3" 80mm
very fine tips



M-5.SA
M-5.S

3" 80mm
extra fine tips



M-AC.SA
M-AC.S

3 1/2" 90mm
strong tips, serrated grips



M-HD.SA
M-HD.S

3 1/2" 90mm
dove tailed, serrated tips and grips

High Precision Reverse Action Tweezers

Specially intended for applications where a high precise self-closing action is required (e.g. microscopy).
Extra fine tips in anti-acid/anti-magnetic stainless steel (SA).



2AX.SA

4 3/4" 120mm
flat accurate round tips



3X.SA

4 3/4" 120mm
very sharp, fine



4X.SA

4 1/4" 110mm
extra fine tips



5AX.SA

4 1/2" 115mm
extra fine tips, superior finish



5TTHX.SA

4 1/4" 110mm
anti capillary, extra fine, with lock-ring
for handling electronic microscope grids



5X.SA

4 1/4" 110mm
extra fine tips, superior finish



7X.SA

4 1/2" 115mm
very fine, curved

Ergonomic ESD Cushion Grip Tweezers

Anti-magnetic precision tweezers with soft ESD ergonomic cushion grips (resistivity 10E8) for an enhanced operator comfort. For more information on our ESD Ergonomic Handle (DR) see page 44.



00.SA.DR

5" 125mm
flat edges, thick



2A.SA.DR

5" 125mm
strong, sharp, rounded tips



3.SA.DR

5" 125mm
very sharp and superior finish



3C.SA.DR

4 1/2" 115mm
very sharp and superior finish




5.SA.DR

4 1/2" 115mm
extra fine tips



7.SA.DR

4 3/4" 120mm
fine curved tips



15AGW.DR

43/4" 120mm
for cutting hairsprings




AA.SA.DR

5" 130mm
precision tips


Super Slim Tweezers

Long and slender tweezers for multiple precision applications especially suitable for working near heat sources.




60.SA

5 1/2" 140mm
precision relieved tips



64A.SA

5 1/2" 140mm
bent, rounded tips



65A.SA
65A.S
65A.NC
65A.TA

5 1/2" 140mm
very fine bent tips



SS.SA
SS.S
SS.NC
SS.TA

5 1/2" 140mm
extra fine tips



SS6.SA
SS6.TA

6" 150mm
extra fine tips



SSF.SA
SSF.NC

5 1/2" 140mm
extra fine, 2mm tips touch



SSL.SA

6" 150mm
as SS6, for max visibility

Flat Tip Tweezers

Smooth scratch proof tips usefull tips for handling electronics sensitive parts.



33A.SA

4 1/2" 115 mm
flat round tips



34A.SA

4 3/4" 120 mm
smooth to hold delicate parts



35A.SA

4 3/4" 120mm
same use as 34A



125.SA

4 3/4" 120 mm
smooth tips, no scratch



125A.SA

4 3/4" 120 mm
Same as 125 but elongated tips



126.SA

4 1/4" 110 mm
round, flat tips



127.SA

4" 105mm
thin, square tips



128.SA

4" 105mm
same as 127, bent tips