

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[SECURITY PRODUCTS](#) > [COLOR CAMERAS](#) > [COLOR CAMERAS WITH HOUSING](#) > [COLOR CAMERAS WITH HOUSING](#) >



COLOUR MICROCAMERA

Order Code: CAMCOLH2U



Features

- ? optional microphone: CAMCOLH2/MIC

Specifications

- ? image sensor: 1/4" Sony CCD
- ? horizontal resolution: 420 TV lines
- ? effective pixels: 510(H) X 492(V) NTSC
- ? scanning system: 2:1 internal
- ? synchronisation: internal
- ? S/N ratio: >48dB
- ? gamma correction: R=0.45
- ? min. illumination: 0.5 lux
- ? video out signal: 1.0Vp-p / 75 ohms
- ? BLC: auto
- ? lens: 3.7mm super cone pinhole lens
- ? horizontal view angle: 63.5°
- ? power supply: 12VDC adapter
- ? current consumption: 120mA max.
- ? gain control: auto
- ? white balance: auto
- ? AGC: auto
- ? electronic shutter: 1/50 -1/100000 sec
- ? operating temperature: 14°F~140°F
- ? cable: 31 1/2"
- ? dimensions: 15/32" x 15/32" x 25/32"
- ? weight: 2.68 oz

Files

- ? [EN- FR- NL- ES- DE](#)

Stock Info

- ? Inner carton:
- ? Outer Carton:
- ? EAN Barcode:
- ? Packaging: