





DATE	STM	REVISION RECORD	DMN.	CK.



PANEL CUT-OUT

THIS DOCUMENT CONTAINS INFORMATION WHICH IS THE EXCLUSIVE PROPERTY OF APEM COMPONENTS, INC. DISTRIBUTION, REPRODUCTION OR USE BY OTHERS IS NOT PERMITTED WITHOUT THE EXPRESS WRITTEN CONSENT OF APEM COMPONENTS, INC.

Q.A. INSPECT. Δ DESIGNATES CRITICAL DIMENSION ● = COMMON SCHEMATIC		APEM CONFIDENTIAL THIS DOCUMENT CONTAINS INFORMATION WHICH IS THE EXCLUSIVE PROPERTY OF APEM COMPONENTS, INC. DISTRIBUTION, REPRODUCTION OR USE BY OTHERS IS NOT PERMITTED WITHOUT THE EXPRESS WRITTEN CONSENT OF APEM COMPONENTS, INC.		DATE 05/03/99		DRAWING NUMBER B1521		REV —	
TOLERANCES (EXCEPT AS NOTED) DECIMAL ± .012 [0.30]		INCH (MM)		SCALE 1.5:1		DRAWN PJD		APPROVED	
FRACTIONAL ± —		ANGULAR ± —		TITLE AV02820KMZQ		WAKEFIELD, MA.		—	

DESCRIPTION: DOUBLE POLE DOUBLE THROW
MOMENTARY SNAP-ACTING PUSH-BUTTON
ANTI-VANDAL SWITCH

SPECIFICATIONS:

CONTACT RATING: 6A @ 125VAC, 3A @ 250VAC,
or 7A @ 30VDC
ELECTRICAL LIFE: 60,000 CYCLES MIN.
INITIAL CONTACT RESISTANCE: 20 MOHMS MAX.
at 3VDC, 0.1A
INSULATION RESISTANCE: > 200,000 MOHMS
BETWEEN TERMINALS AND CASE GROUND
DIELECTRIC STRENGTH: > 1,000VAC FOR 1 MIN.
BETWEEN TERMINALS AND CASE GROUND
OPERATING TEMPERATURE RANGE: -30°C to +80°C