

TRANSIENT VOLTAGE SUPPRESSOR 500 WATT SERIES

Glass Passivated Die Plus Dual Heat Strips

Features:

- Low Profile
- Broad Voltage Range Available - - 6.8 to 200 Volts
- Broad Spectrum Transient Suppression
- Rapid Response - - 4 nanoseconds typical
- Built-in Heat Absorbing Terminations
- Electrically Similar to Mil-Prf-19500/516

Applications:


- Connector I/O Surge Suppression
- Data Line Protection

Description: This is a bipolar transient voltage suppressor series extending from 6.8 volts to 200 volts intended for surface mount applications.

Each device comes as a "Cell" with its own heat absorbing terminals pre-bonded at high temperature. This permits mounting on printed circuit boards that cannot provide their own heat sinking. Each terminal is silver plated and is solderable permitting solder down attachment with a very small footprint. Each unit is bi-symmetrical so any orientation can be used.

ELECTRICAL CHARACTERISTICS

PARAMETER	SYMBOL	Test Conditions	Min	TYP	Max.	Units
Response Turn-on Time	ton			2	5	ns
Transient Energy Pulse (Cell)	Ep 1	10uS rise, I= 0.5Ip at t=100us (exponential decay)	1500			W
Transient Energy Pulse (Cell)	Ep 2	10uS rise, I= 0.5Ip at t=1.0mS (exponential decay)	500			W
Transient Energy Pulse (Cell)	Ep 3	10uS rise, I= 0.5Ip at t=10mS (exponential decay)	150			W
Transient Energy Pulse (Cell)	Ep 4	10uS rise, I= 0.5Ip at t=50mS (exponential decay)	70			W
Transient Energy Pulse (Cell)	Ep 5	10uS rise, I= 0.5Ip at t=50mS (step pulse)	50			W
Electrical Parameters				See Table		
Maximum Solder Temperature	Tmax	10 second exposure			300	°C
Thermal Resistance (J-C)	ΘJC	Assume heat sink on terminal strip ends		18	30	°C/W




Note 1: "Die Only" configuration requires user to provide adequate energy absorption.

Note 2: Terminal strips are 0.009" to 0.011" thick copper with nickel and silver plate.


SEN-R-956-XXX 500Watt TVS Series

Part Number	Nominal Vz (V)	Iz (mA)	Vz min @ Iz (V)	Vz max @ Iz (V)	TC (nom) of Vz (%.°C)	Vr (V)	Ir max @ Vr (uA)	Vcc (V)	Ip (A)
SEN-R-956-001	6.8	10	6.40	7.25	0.050	5.0	1600	9.2	54.3
SEN-R-956-002	7.2	10	6.67	7.67	0.060	6.0	1600	10.3	48.5
SEN-R-956-003	7.8	10	7.22	8.30	0.060	6.5	1000	11.2	44.6
SEN-R-956-004	8.4	10	7.78	8.95	0.060	7.0	400	12.0	41.7
SEN-R-956-005	9.0	1	8.33	9.58	0.070	7.5	200	12.9	38.8
SEN-R-956-006	9.6	1	8.89	10.23	0.070	8.0	100	13.6	36.8
SEN-R-956-007	10	1	9.44	10.82	0.070	8.5	20	14.4	34.7
SEN-R-956-008	11	1	10.00	11.50	0.080	9.0	10	15.4	32.5
SEN-R-956-009	12	1	11.10	12.80	0.080	10.0	5	17.0	29.4
SEN-R-956-010	13	1	12.20	14.00	0.080	11.0	5	18.2	27.5
SEN-R-956-011	14	1	13.30	15.50	0.085	12.0	5	19.9	25.1
SEN-R-956-012	15	1	14.40	16.50	0.085	13.0	5	21.5	23.3
SEN-R-956-013	17	1	15.60	17.90	0.085	14.0	5	23.2	21.6
SEN-R-956-014	18	1	16.70	19.20	0.090	15.0	5	24.4	20.5
SEN-R-956-015	19	1	17.80	20.50	0.090	16.0	5	26.0	19.2
SEN-R-956-016	20	1	18.90	21.70	0.090	17.0	5	27.6	18.1
SEN-R-956-017	22	1	20.00	23.30	0.095	18.0	5	29.2	17.1
SEN-R-956-018	24	1	22.20	25.50	0.095	20.0	5	32.4	15.4
SEN-R-956-019	26	1	24.40	28.00	0.095	22.0	5	35.5	14.1
SEN-R-956-020	29	1	26.70	30.70	0.095	24.0	5	38.9	12.9
SEN-R-956-021	31	1	28.90	33.20	0.095	26.0	5	42.1	11.9
SEN-R-956-022	33	1	31.10	35.80	0.095	28.0	5	45.4	11.0
SEN-R-956-023	36	1	33.30	38.30	0.095	30.0	5	48.4	10.3
SEN-R-956-024	39	1	36.70	42.20	0.100	33.0	5	53.3	9.4
SEN-R-956-025	43	1	40.00	46.00	0.100	36.0	5	58.1	8.6
SEN-R-956-026	48	1	44.40	51.10	0.100	40.0	5	64.5	7.8
SEN-R-956-027	51	1	47.80	54.90	0.100	43.0	5	69.4	7.2
SEN-R-956-028	54	1	50.00	57.50	0.100	45.0	5	72.7	6.9
SEN-R-956-029	57	1	53.30	61.30	0.100	48.0	5	77.4	6.5
SEN-R-956-030	61	1	56.7	65.2	0.100	51.0	5	82.4	6.1
SEN-R-956-031	65	1	60.0	69.0	0.100	54.0	5	87.1	5.7
SEN-R-956-032	69	1	64.4	74.1	0.105	58.0	5	93.6	5.3
SEN-R-956-033	72	1	66.7	76.7	0.105	60.0	5	96.8	5.2
SEN-R-956-034	76	1	71.1	81.8	0.105	64.0	5	103.0	4.9
SEN-R-956-035	84	1	77.8	89.5	0.110	70.0	5	113.0	4.4
SEN-R-956-036	90	1	83.3	95.8	0.110	75.0	5	121.0	4.1
SEN-R-956-037	93	1	86.7	99.7	0.110	78.0	5	126.0	4.0
SEN-R-956-038	101	1	94.4	108.2	0.110	85.0	5	137.0	3.6
SEN-R-956-039	108	1	100.0	115.5	0.110	90.0	5	146.0	3.4
SEN-R-956-040	120	1	111.0	128.0	0.110	100.0	5	162.0	3.1
SEN-R-956-041	131	1	122.0	140.5	0.110	110.0	5	177.0	2.8
SEN-R-956-042	143	1	133.0	153.0	0.110	120.0	5	193.0	2.6
SEN-R-956-043	155	1	144.0	165.5	0.110	130.0	5	209.0	2.4
SEN-R-956-044	180	1	167.0	192.5	0.110	150.0	5	243.0	2.1
SEN-R-956-045	192	1	178.0	205.0	0.110	160.0	5	259.0	1.9
SEN-R-956-046	203	1	189.0	217.5	0.110	170.0	5	275.0	1.8


Clamp Power vs Time for Sensitron 500W TVS Series



Exponential Decay Pulse Waveform



Reverse Junction Capacitance for Sensitron 500W TVS



TECHNICAL DATA

DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the Sensitron Semiconductor sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall Sensitron Semiconductor be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). Sensitron Semiconductor assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall Sensitron Semiconductor be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or Sensitron Semiconductor.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of Sensitron Semiconductor.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations.